

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224768

Luminaire Tested: **LSSQWM2B10FL409050D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409050D010 2LBDL*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 841.9 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224768

CATALOG NUMBER: LSSQWM2B10FL409050D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224768

CATALOG NUMBER: LSSQWM2B10FL409050D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	762181
5°	748295
10°	665185
15°	523158
20°	348107
25°	199847
30°	100949
35°	47475
40°	19113
45°	9477
50°	5182
55°	3647
60°	3331
65°	2016
70°	2492
75°	1646
80°	2454
85°	0



TEST NUMBER: P224768

CATALOG NUMBER: LSSQWM2B10FL409050D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.3	20.9
10°-20°	353.4	42.0
20°-30°	219.8	26.1
30°-40°	67.6	8.0
40°-50°	14.9	1.8
50°-60°	5.3	0.6
60°-70°	2.7	0.3
70°-80°	1.6	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	749.5	89.0
0°-40°	817.1	97.0
0°-60°	837.2	99.4
0°-90°	841.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	841.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1968	
5°	1924	176
15°	1305	353
25°	468	220
35°	100	68
45°	17	15
55°	5	5
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P224768

CATALOG NUMBER: LSSQWM2B10FL409050D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1967.7
2.5°	1959.1
5°	1924.5
7.5°	1837.0
10°	1691.2
12.5°	1516.3
15°	1304.6
17.5°	1073.5
20°	844.5
22.5°	640.4
25°	467.6
27.5°	329.4
30°	225.7
32.5°	152.3
35°	100.4
37.5°	60.5
40°	37.8
42.5°	25.9
45°	17.3
47.5°	11.9
50°	8.6
52.5°	7.6
55°	5.4
57.5°	4.3
60°	4.3
62.5°	3.2
65°	2.2
67.5°	2.2
70°	2.2
72.5°	2.2
75°	1.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)