

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222945

Luminaire Tested: **LSR2B15NFL259024D010 2LBDLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P222945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B15NFL259024D010 2LBDLC\*MB  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
NARROW FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 910.5 lumens  
Efficiency: N/A  
Efficacy: 63.7 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P222945

CATALOG NUMBER: LSR2B15NFL259024D010 2LBDLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P222945

CATALOG NUMBER: LSR2B15NFL259024D010 2LBDLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97			97																
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95			95																
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92			92																
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90			90																
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88			88																
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86			86																
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84			84																
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82			82																
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80			80																
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79			79																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2092327
5°	1931880
10°	1307636
15°	444881
20°	163398
25°	86632
30°	44503
35°	20759
40°	6826
45°	3451
50°	1627
55°	608
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222945

CATALOG NUMBER: LSR2B15NFL259024D010 2LBDLC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	422.6	46.4
10°-20°	355.3	39.0
20°-30°	97.5	10.7
30°-40°	28.4	3.1
40°-50°	5.3	0.6
50°-60°	1.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	875.5	96.2
0°-40°	903.9	99.3
0°-60°	910.4	100.0
0°-90°	910.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	910.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5402	
5°	4968	423
15°	1109	355
25°	203	98
35°	44	28
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222945

CATALOG NUMBER: LSR2B15NFL259024D010 2LBDLC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5401.7
1°	5370.3
2°	5314.7
3°	5234.8
4°	5125.4
5°	4968.5
6°	4754.1
7°	4486.0
8°	4158.6
9°	3772.1
10°	3324.6
11°	2834.0
12°	2323.7
13°	1836.7
14°	1421.5
15°	1109.4
17.5°	626.0
20°	396.4
22.5°	282.5
25°	202.7
27.5°	143.5
30°	99.5
32.5°	70.0
35°	43.9
37.5°	17.9
40°	13.5
42.5°	9.9
45°	6.3
47.5°	3.6
50°	2.7
52.5°	1.8
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222945

CATALOG NUMBER: LSR2B15NFL259024D010 2LBDLC\*MB

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)