

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225519

Luminaire Tested: **LSSQWM2B15FL408050D010 2LBDL\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225519  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14832)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B15FL408050D010 2LBDL\*H  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1350.5 lumens  
Efficiency: N/A  
Efficacy: 94.4 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225519

CATALOG NUMBER: LSSQWM2B15FL408050D010 2LBDL\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P225519

CATALOG NUMBER: LSSQWM2B15FL408050D010 2LBDL\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90			90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86			86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82			82
5	97	90	85	81	96	89	84	81	87	83	80	86	82	80	84	81	79	78			78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74			74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	75	72	71			71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68			68
9	83	75	70	67	82	75	70	67	74	69	66	73	69	66	72	69	66	65			65
10	80	72	67	64	79	72	67	64	71	67	64	70	66	64	70	66	63	62			62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1187138
5°	1147619
10°	1012606
15°	797729
20°	548191
25°	331056
30°	179444
35°	92208
40°	45103
45°	21364
50°	11208
55°	7496
60°	4338
65°	1741
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225519

CATALOG NUMBER: LSSQWM2B15FL408050D010 2LBDL\*H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	269.7	20.0
10°-20°	541.6	40.1
20°-30°	361.8	26.8
30°-40°	131.0	9.7
40°-50°	33.8	2.5
50°-60°	10.1	0.7
60°-70°	2.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1173.1	86.9
0°-40°	1304.1	96.6
0°-60°	1348.0	99.8
0°-90°	1350.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1350.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3065	
5°	2952	270
15°	1989	542
25°	775	362
35°	195	131
45°	39	34
55°	11	10
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225519

CATALOG NUMBER: LSSQWM2B15FL408050D010 2LBDL\*H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3064.8
2.5°	3037.0
5°	2951.5
7.5°	2795.5
10°	2574.5
12.5°	2303.3
15°	1989.3
17.5°	1655.0
20°	1329.9
22.5°	1030.9
25°	774.6
27.5°	564.7
30°	401.2
32.5°	282.3
35°	195.0
37.5°	135.6
40°	89.2
42.5°	57.6
45°	39.0
47.5°	27.9
50°	18.6
52.5°	14.9
55°	11.1
57.5°	7.4
60°	5.6
62.5°	3.7
65°	1.9
67.5°	1.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)