

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222929

Luminaire Tested: **LSSQ2B15NFL259024D010 2LBD*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B15NFL259024D010 2LBD*B
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 980.5 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222929

CATALOG NUMBER: LSSQ2B15NFL259024D010 2LBD*B

Luminous Intensity Polar Plot





TEST NUMBER: P222929

CATALOG NUMBER: LSSQ2B15NFL259024D010 2LBD*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|-----|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 | | | | | | | | | | | | | | | |
| 1 | 115 | 113 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 100 | 99 | 97 | | | | 97 | | | | | | | | | | | | | | | |
| 2 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99 | 98 | 98 | 97 | 96 | 95 | | | | 95 | | | | | | | | | | | | | | | |
| 3 | 109 | 105 | 101 | 99 | 107 | 103 | 100 | 98 | 101 | 98 | 96 | 99 | 97 | 95 | 96 | 95 | 93 | 92 | | | | 92 | | | | | | | | | | | | | | | |
| 4 | 106 | 101 | 97 | 95 | 104 | 100 | 97 | 94 | 98 | 95 | 93 | 96 | 94 | 92 | 95 | 93 | 91 | 90 | | | | 90 | | | | | | | | | | | | | | | |
| 5 | 103 | 98 | 94 | 91 | 102 | 97 | 94 | 91 | 95 | 92 | 90 | 94 | 91 | 89 | 93 | 90 | 89 | 88 | | | | 88 | | | | | | | | | | | | | | | |
| 6 | 101 | 95 | 91 | 89 | 99 | 94 | 91 | 88 | 93 | 90 | 88 | 92 | 89 | 87 | 91 | 88 | 87 | 86 | | | | 86 | | | | | | | | | | | | | | | |
| 7 | 98 | 92 | 89 | 86 | 97 | 92 | 88 | 86 | 91 | 88 | 85 | 90 | 87 | 85 | 89 | 86 | 85 | 84 | | | | 84 | | | | | | | | | | | | | | | |
| 8 | 96 | 90 | 86 | 84 | 95 | 90 | 86 | 84 | 89 | 86 | 83 | 88 | 85 | 83 | 87 | 85 | 83 | 82 | | | | 82 | | | | | | | | | | | | | | | |
| 9 | 94 | 88 | 84 | 82 | 93 | 88 | 84 | 82 | 87 | 84 | 82 | 86 | 83 | 81 | 85 | 83 | 81 | 80 | | | | 80 | | | | | | | | | | | | | | | |
| 10 | 92 | 86 | 82 | 80 | 91 | 86 | 82 | 80 | 85 | 82 | 80 | 84 | 82 | 80 | 84 | 81 | 79 | 79 | | | | 79 | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2253153 |
| 5° | 2080411 |
| 10° | 1408169 |
| 15° | 479087 |
| 20° | 175970 |
| 25° | 93299 |
| 30° | 47947 |
| 35° | 22366 |
| 40° | 7332 |
| 45° | 3725 |
| 50° | 1748 |
| 55° | 675 |
| 60° | 775 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P222929

CATALOG NUMBER: LSSQ2B15NFL259024D010 2LBD*B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 455.1 | 46.4 |
| 10°-20° | 382.7 | 39.0 |
| 20°-30° | 105.0 | 10.7 |
| 30°-40° | 30.6 | 3.1 |
| 40°-50° | 5.7 | 0.6 |
| 50°-60° | 1.3 | 0.1 |
| 60°-70° | 0.1 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 942.8 | 96.2 |
| 0°-40° | 973.4 | 99.3 |
| 0°-60° | 980.4 | 100.0 |
| 0°-90° | 980.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 980.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 5817 | |
| 5° | 5350 | 455 |
| 15° | 1195 | 383 |
| 25° | 218 | 105 |
| 35° | 47 | 31 |
| 45° | 7 | 6 |
| 55° | 1 | 1 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P222929

CATALOG NUMBER: LSSQ2B15NFL259024D010 2LBD*B

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 5816.9 |
| 1° | 5783.1 |
| 2° | 5723.3 |
| 3° | 5637.3 |
| 4° | 5519.5 |
| 5° | 5350.5 |
| 6° | 5119.6 |
| 7° | 4830.9 |
| 8° | 4478.4 |
| 9° | 4062.1 |
| 10° | 3580.2 |
| 11° | 3051.9 |
| 12° | 2502.4 |
| 13° | 1977.9 |
| 14° | 1530.8 |
| 15° | 1194.7 |
| 17.5° | 674.1 |
| 20° | 426.9 |
| 22.5° | 304.2 |
| 25° | 218.3 |
| 27.5° | 154.5 |
| 30° | 107.2 |
| 32.5° | 75.3 |
| 35° | 47.3 |
| 37.5° | 19.3 |
| 40° | 14.5 |
| 42.5° | 10.6 |
| 45° | 6.8 |
| 47.5° | 3.9 |
| 50° | 2.9 |
| 52.5° | 1.9 |
| 55° | 1.0 |
| 57.5° | 1.0 |
| 60° | 1.0 |
| 62.5° | 0.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P222929

CATALOG NUMBER: LSSQ2B15NFL259024D010 2LBD*B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)