

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223112

Luminaire Tested: **LSSQWM2B15NFL258050D010 2LBD**MW***

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223112
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15NFL258050D010 2LBD*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1427.7 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223112

CATALOG NUMBER: LSSQWM2B15NFL258050D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223112

CATALOG NUMBER: LSSQWM2B15NFL258050D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	94	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	86
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	84
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	82
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84	83	82	80
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	79
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	78	77
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	78	77	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3280821
5°	3029262
10°	2050424
15°	697597
20°	256227
25°	135824
30°	69819
35°	32580
40°	10669
45°	5368
50°	2531
55°	945
60°	1085
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223112

CATALOG NUMBER: LSSQWM2B15NFL258050D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	662.7	46.4
10°-20°	557.2	39.0
20°-30°	152.9	10.7
30°-40°	44.6	3.1
40°-50°	8.2	0.6
50°-60°	1.9	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1372.8	96.2
0°-40°	1417.4	99.3
0°-60°	1427.5	100.0
0°-90°	1427.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1427.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8470	
5°	7791	663
15°	1740	557
25°	318	153
35°	69	45
45°	10	8
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223112

CATALOG NUMBER: LSSQWM2B15NFL258050D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8470.0
1°	8420.8
2°	8333.6
3°	8208.4
4°	8036.9
5°	7790.8
6°	7454.7
7°	7034.2
8°	6520.9
9°	5914.8
10°	5213.1
11°	4443.8
12°	3643.7
13°	2880.1
14°	2228.9
15°	1739.6
17.5°	981.6
20°	621.6
22.5°	443.0
25°	317.8
27.5°	225.0
30°	156.1
32.5°	109.7
35°	68.9
37.5°	28.1
40°	21.1
42.5°	15.5
45°	9.8
47.5°	5.6
50°	4.2
52.5°	2.8
55°	1.4
57.5°	1.4
60°	1.4
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223112

CATALOG NUMBER: LSSQWM2B15NFL258050D010 2LBD*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)