

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223461

Luminaire Tested: **LSR2B15NFL258027D010 2LBDLC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223461  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B15NFL258027D010 2LBDLC\*MMS  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
NARROW FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1257.1 lumens  
Efficiency: N/A  
Efficacy: 87.9 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223461

CATALOG NUMBER: LSR2B15NFL258027D010 2LBDLC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P223461

CATALOG NUMBER: LSR2B15NFL258027D010 2LBDLC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2888788
5°	2667266
10°	1805385
15°	614227
20°	225600
25°	119583
30°	61455
35°	28703
40°	9405
45°	4766
50°	2230
55°	810
60°	930
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223461

CATALOG NUMBER: LSR2B15NFL258027D010 2LBDLC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	583.5	46.4
10°-20°	490.6	39.0
20°-30°	134.6	10.7
30°-40°	39.3	3.1
40°-50°	7.3	0.6
50°-60°	1.6	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1208.8	96.2
0°-40°	1248.0	99.3
0°-60°	1256.9	100.0
0°-90°	1257.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1257.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7458	
5°	6860	584
15°	1532	491
25°	280	135
35°	61	39
45°	9	7
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223461

CATALOG NUMBER: LSR2B15NFL258027D010 2LBDLC\*MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7457.9
1°	7414.6
2°	7337.8
3°	7227.6
4°	7076.5
5°	6859.8
6°	6563.9
7°	6193.7
8°	5741.7
9°	5208.0
10°	4590.1
11°	3912.8
12°	3208.3
13°	2535.9
14°	1962.6
15°	1531.7
17.5°	864.3
20°	547.3
22.5°	390.0
25°	279.8
27.5°	198.1
30°	137.4
32.5°	96.6
35°	60.7
37.5°	24.8
40°	18.6
42.5°	13.6
45°	8.7
47.5°	5.0
50°	3.7
52.5°	2.5
55°	1.2
57.5°	1.2
60°	1.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223461

CATALOG NUMBER: LSR2B15NFL258027D010 2LBDLC\*MMS

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)