

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B15WFL558050D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15WFL558050D010 2LBDC*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1359.4 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSSQWM2B15WFL558050D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558050D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93	93	93	93	93	93	93	93	93	93	93																
	2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86	86	86	86	86	86	86	86	86	86	86																
	3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80	80	80	80	80	80	80	80	80	80	80																
	4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74	74	74	74	74	74	74	74	74	74	74																
	5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69	69	69	69	69	69	69	69	69	69	69																
	6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64	64	64	64	64	64	64	64	64	64	64																
	7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60	60	60	60	60	60	60	60	60	60	60																
	8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56	56	56	56	56	56	56	56	56	56	56																
	9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53	53	53	53	53	53	53	53																
	10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49	49	49	49	49	49	49	49	49	49	49																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	637688
5°	633630
10°	589038
15°	517102
20°	445758
25°	381188
30°	302488
35°	210849
40°	133440
45°	81402
50°	48148
55°	26337
60°	5733
65°	5133
70°	4190
75°	5537
80°	4238
85°	8444



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558050D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.2	11.1
10°-20°	359.1	26.4
20°-30°	405.2	29.8
30°-40°	280.3	20.6
40°-50°	119.5	8.8
50°-60°	34.5	2.5
60°-70°	5.1	0.4
70°-80°	3.2	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	915.6	67.3
0°-40°	1195.9	88.0
0°-60°	1349.9	99.3
0°-90°	1359.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1359.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1646	
5°	1630	151
15°	1290	359
25°	892	405
35°	446	280
45°	149	119
55°	39	35
65°	6	5
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558050D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1646.3
2.5°	1644.4
5°	1629.6
7.5°	1579.4
10°	1497.6
12.5°	1397.3
15°	1289.5
17.5°	1178.0
20°	1081.4
22.5°	990.4
25°	891.9
27.5°	787.8
30°	676.3
32.5°	555.6
35°	445.9
37.5°	345.6
40°	263.9
42.5°	198.8
45°	148.6
47.5°	107.8
50°	79.9
52.5°	57.6
55°	39.0
57.5°	16.7
60°	7.4
62.5°	5.6
65°	5.6
67.5°	3.7
70°	3.7
72.5°	3.7
75°	3.7
77.5°	1.9
80°	1.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)