

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225003

Luminaire Tested: **LSRWM2B15FL408027D010 2LBDL\*LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225003  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSRWM2B15FL408027D010 2LBDL\*LI  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1276.8 lumens  
Efficiency: N/A  
Efficacy: 89.3 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225003

CATALOG NUMBER: LSRWM2B15FL408027D010 2LBDL\*LI

### Luminous Intensity Polar Plot





TEST NUMBER: P225003

CATALOG NUMBER: LSRWM2B15FL408027D010 2LBDL\*LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76	76	76	76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73	73	73	73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70	70	70	70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67	67	67	67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65	65	65	65

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1224788
5°	1176975
10°	1024563
15°	800055
20°	532074
25°	304686
30°	151490
35°	69605
40°	27912
45°	12764
50°	5906
55°	3309
60°	1937
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225003

CATALOG NUMBER: LSRWM2B15FL408027D010 2LBDL\*LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	275.5	21.6
10°-20°	541.0	42.4
20°-30°	334.8	26.2
30°-40°	100.2	7.8
40°-50°	20.1	1.6
50°-60°	4.9	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1151.3	90.2
0°-40°	1251.5	98.0
0°-60°	1276.5	100.0
0°-90°	1276.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1276.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3162	
5°	3027	276
15°	1995	541
25°	713	335
35°	147	100
45°	23	20
55°	5	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225003

CATALOG NUMBER: LSRWM2B15FL408027D010 2LBDL\*LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3162.0
1°	3144.8
2°	3128.9
3°	3097.0
4°	3067.5
5°	3027.0
6°	2971.8
7°	2901.9
8°	2812.3
9°	2710.4
10°	2604.9
11°	2495.7
12°	2379.2
13°	2257.7
14°	2127.6
15°	1995.1
17.5°	1645.4
20°	1290.8
22.5°	976.7
25°	712.9
27.5°	500.6
30°	338.7
32.5°	223.3
35°	147.2
37.5°	92.0
40°	55.2
42.5°	35.6
45°	23.3
47.5°	14.7
50°	9.8
52.5°	7.4
55°	4.9
57.5°	3.7
60°	2.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P225003

CATALOG NUMBER: LSRWM2B15FL408027D010 2LBDL\*LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)