

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225149

Luminaire Tested: **LSSQ2B15FL409050D010 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B15FL409050D010 2LBD*GPH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1223.0 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225149

CATALOG NUMBER: LSSQ2B15FL409050D010 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P225149

CATALOG NUMBER: LSSQ2B15FL409050D010 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	100	108	104	101	98	101	99	96	98	96	94	95	94	92	91			91
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87			87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83			83
5	98	91	86	83	96	90	85	82	88	84	81	87	83	81	85	82	80	79			79
6	94	87	82	78	93	86	81	78	85	81	78	83	80	77	82	79	77	75			75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72			72
8	87	80	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69			69
9	84	76	72	68	83	76	71	68	75	71	68	74	70	68	73	70	68	66			66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1109475
5°	1087040
10°	965879
15°	757829
20°	509650
25°	296522
30°	148538
35°	69322
40°	32311
45°	13640
50°	6568
55°	4187
60°	2402
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225149

CATALOG NUMBER: LSSQ2B15FL409050D010 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.9	20.9
10°-20°	513.0	41.9
20°-30°	324.3	26.5
30°-40°	100.9	8.2
40°-50°	22.4	1.8
50°-60°	5.7	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1093.2	89.4
0°-40°	1194.1	97.6
0°-60°	1222.2	99.9
0°-90°	1223.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1223.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2864	
5°	2796	256
15°	1890	513
25°	694	324
35°	147	101
45°	25	22
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225149

CATALOG NUMBER: LSSQ2B15FL409050D010 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2864.3
2.5°	2851.8
5°	2795.7
7.5°	2663.1
10°	2455.7
12.5°	2193.8
15°	1889.8
17.5°	1560.8
20°	1236.4
22.5°	944.9
25°	693.8
27.5°	486.5
30°	332.1
32.5°	219.8
35°	146.6
37.5°	98.2
40°	63.9
42.5°	39.0
45°	24.9
47.5°	17.2
50°	10.9
52.5°	7.8
55°	6.2
57.5°	4.7
60°	3.1
62.5°	1.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)