

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225361

Luminaire Tested: **LSR2B15FL409027D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15FL409027D010 2LBDC*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 930.2 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225361

CATALOG NUMBER: LSR2B15FL409027D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P225361

CATALOG NUMBER: LSR2B15FL409027D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86		
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82		
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79		
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75		
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72		
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	842129
5°	826760
10°	734960
15°	578016
20°	384628
25°	220832
30°	111549
35°	52488
40°	21136
45°	10463
50°	5725
55°	4052
60°	3719
65°	2200
70°	2718
75°	1796
80°	2677
85°	0



TEST NUMBER: P225361

CATALOG NUMBER: LSR2B15FL409027D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.7	20.9
10°-20°	390.5	42.0
20°-30°	242.9	26.1
30°-40°	74.7	8.0
40°-50°	16.4	1.8
50°-60°	5.9	0.6
60°-70°	3.0	0.3
70°-80°	1.7	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	828.1	89.0
0°-40°	902.8	97.0
0°-60°	925.0	99.4
0°-90°	930.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	930.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2174	
5°	2126	195
15°	1441	390
25°	517	243
35°	111	75
45°	19	16
55°	6	6
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P225361

CATALOG NUMBER: LSR2B15FL409027D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2174.1
2.5°	2164.5
5°	2126.3
7.5°	2029.7
10°	1868.6
12.5°	1675.3
15°	1441.4
17.5°	1186.1
20°	933.1
22.5°	707.6
25°	516.7
27.5°	363.9
30°	249.4
32.5°	168.2
35°	111.0
37.5°	66.8
40°	41.8
42.5°	28.6
45°	19.1
47.5°	13.1
50°	9.5
52.5°	8.4
55°	6.0
57.5°	4.8
60°	4.8
62.5°	3.6
65°	2.4
67.5°	2.4
70°	2.4
72.5°	2.4
75°	1.2
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)