

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B15WFL559027D010 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14804)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15WFL559027D010 2LBD*WH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1000.3 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.81
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																											
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87																											
3	102	96	90	86	100	94	90	86	92	88	84	89	86	83	87	84	82	80																											
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74																											
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69																											
6	87	78	72	68	86	77	71	67	76	71	67	74	70	66	73	69	66	64																											
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60																											
8	79	69	63	59	77	68	63	59	67	62	58	66	61	58	65	61	58	56																											
9	75	65	59	55	74	64	59	55	64	58	55	63	58	54	62	57	54	53																											
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	500722
5°	483427
10°	437688
15°	383446
20°	330135
25°	280666
30°	220593
35°	153302
40°	99359
45°	59435
50°	34770
55°	19449
60°	7437
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.5	11.4
10°-20°	266.2	26.6
20°-30°	298.2	29.8
30°-40°	205.0	20.5
40°-50°	88.1	8.8
50°-60°	26.9	2.7
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.9	67.9
0°-40°	883.9	88.4
0°-60°	998.8	99.9
0°-90°	1000.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1000.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1293	
5°	1243	114
15°	956	266
25°	657	298
35°	324	205
45°	108	88
55°	29	27
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBD*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1292.7
2.5°	1279.0
5°	1243.3
7.5°	1185.6
10°	1112.8
12.5°	1035.8
15°	956.2
17.5°	872.4
20°	800.9
22.5°	729.5
25°	656.7
27.5°	579.7
30°	493.2
32.5°	405.3
35°	324.2
37.5°	254.1
40°	196.5
42.5°	147.0
45°	108.5
47.5°	79.7
50°	57.7
52.5°	39.8
55°	28.8
57.5°	19.2
60°	9.6
62.5°	1.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)