

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224923

Luminaire Tested: **LSSQWM2B15FL409050D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409050D010 2LBD*H
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1208.6 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224923

CATALOG NUMBER: LSSQWM2B15FL409050D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224923

CATALOG NUMBER: LSSQWM2B15FL409050D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 95 | | | 95 |
| 2 | 110 | 106 | 103 | 100 | 108 | 104 | 101 | 99 | 101 | 99 | 97 | 98 | 96 | 94 | 96 | 94 | 93 | 91 | | | 91 |
| 3 | 106 | 100 | 96 | 93 | 104 | 99 | 95 | 92 | 97 | 94 | 91 | 94 | 92 | 90 | 92 | 90 | 88 | 87 | | | 87 |
| 4 | 102 | 96 | 91 | 88 | 100 | 94 | 90 | 87 | 92 | 89 | 86 | 91 | 88 | 85 | 89 | 86 | 84 | 83 | | | 83 |
| 5 | 98 | 91 | 86 | 83 | 96 | 90 | 86 | 82 | 89 | 85 | 82 | 87 | 84 | 81 | 86 | 83 | 80 | 79 | | | 79 |
| 6 | 94 | 87 | 82 | 79 | 93 | 86 | 82 | 78 | 85 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 77 | 76 | | | 76 |
| 7 | 91 | 83 | 78 | 75 | 90 | 83 | 78 | 75 | 82 | 77 | 74 | 80 | 77 | 74 | 79 | 76 | 74 | 73 | | | 73 |
| 8 | 88 | 80 | 75 | 72 | 87 | 79 | 75 | 72 | 78 | 74 | 71 | 77 | 74 | 71 | 77 | 73 | 71 | 70 | | | 70 |
| 9 | 85 | 77 | 72 | 69 | 84 | 76 | 72 | 69 | 75 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 67 | | | 67 |
| 10 | 82 | 74 | 69 | 66 | 81 | 73 | 69 | 66 | 73 | 69 | 66 | 72 | 68 | 66 | 71 | 68 | 65 | 64 | | | 64 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1121018 |
| 5° | 1097538 |
| 10° | 966627 |
| 15° | 758390 |
| 20° | 503632 |
| 25° | 289086 |
| 30° | 145004 |
| 35° | 66957 |
| 40° | 27204 |
| 45° | 12161 |
| 50° | 6327 |
| 55° | 3984 |
| 60° | 1782 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P224923

CATALOG NUMBER: LSSQWM2B15FL409050D010 2LBD*H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 257.8 | 21.3 |
| 10°-20° | 511.9 | 42.4 |
| 20°-30° | 318.1 | 26.3 |
| 30°-40° | 95.9 | 7.9 |
| 40°-50° | 19.6 | 1.6 |
| 50°-60° | 5.0 | 0.4 |
| 60°-70° | 0.3 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1087.7 | 90.0 |
| 0°-40° | 1183.7 | 97.9 |
| 0°-60° | 1208.3 | 100.0 |
| 0°-90° | 1208.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1208.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2894 | |
| 5° | 2823 | 258 |
| 15° | 1891 | 512 |
| 25° | 676 | 318 |
| 35° | 142 | 96 |
| 45° | 22 | 20 |
| 55° | 6 | 5 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P224923

CATALOG NUMBER: LSSQWM2B15FL409050D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2894.1 |
| 1° | 2884.8 |
| 2° | 2871.9 |
| 3° | 2862.5 |
| 4° | 2848.5 |
| 5° | 2822.7 |
| 6° | 2781.8 |
| 7° | 2725.6 |
| 8° | 2644.8 |
| 9° | 2553.6 |
| 10° | 2457.6 |
| 11° | 2355.8 |
| 12° | 2249.3 |
| 13° | 2138.1 |
| 14° | 2016.4 |
| 15° | 1891.2 |
| 17.5° | 1555.3 |
| 20° | 1221.8 |
| 22.5° | 926.9 |
| 25° | 676.4 |
| 27.5° | 477.5 |
| 30° | 324.2 |
| 32.5° | 213.0 |
| 35° | 141.6 |
| 37.5° | 87.8 |
| 40° | 53.8 |
| 42.5° | 35.1 |
| 45° | 22.2 |
| 47.5° | 14.0 |
| 50° | 10.5 |
| 52.5° | 7.0 |
| 55° | 5.9 |
| 57.5° | 3.5 |
| 60° | 2.3 |
| 62.5° | 0.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P224923

CATALOG NUMBER: LSSQWM2B15FL409050D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)