

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B15WFL559027D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15WFL559027D010 2LBDL*H
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 930.2 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B15WFL559027D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																											
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86																											
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80																											
4	96	89	83	79	95	87	82	78	85	81	77	83	79	76	81	78	75	74																											
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	68																											
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64																											
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	59																											
8	78	68	62	58	77	68	62	58	67	61	57	66	61	57	65	60	57	56																											
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	54	52																											
10	71	61	55	51	70	60	55	51	60	54	51	59	54	51	58	54	50	49																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	436384
5°	427903
10°	397766
15°	352167
20°	304867
25°	256305
30°	200689
35°	143419
40°	95769
45°	59380
50°	35554
55°	21340
60°	9529
65°	1283
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	11.0
10°-20°	244.6	26.3
20°-30°	272.8	29.3
30°-40°	191.1	20.5
40°-50°	87.3	9.4
50°-60°	29.2	3.1
60°-70°	3.2	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.5	66.6
0°-40°	810.6	87.1
0°-60°	927.1	99.7
0°-90°	930.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	930.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1127	
5°	1100	102
15°	878	245
25°	600	273
35°	303	191
45°	108	87
55°	32	29
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1126.6
2.5°	1121.1
5°	1100.5
7.5°	1062.1
10°	1011.3
12.5°	946.8
15°	878.2
17.5°	806.9
20°	739.6
22.5°	672.4
25°	599.7
27.5°	525.6
30°	448.7
32.5°	373.2
35°	303.3
37.5°	241.5
40°	189.4
42.5°	144.1
45°	108.4
47.5°	81.0
50°	59.0
52.5°	42.5
55°	31.6
57.5°	22.0
60°	12.3
62.5°	4.1
65°	1.4
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)