

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224603

Luminaire Tested: **LSR2B15FL409030D2WD010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15FL409030D2WD010 2LBDLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 761.4 lumens
Efficiency: N/A
Efficacy: 53.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224603

CATALOG NUMBER: LSR2B15FL409030D2WD010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224603

CATALOG NUMBER: LSR2B15FL409030D2WD010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																			
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91																			
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87																			
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83																			
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	83	80	79																			
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	76																			
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72																			
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69																			
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67																			
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	693078
5°	679745
10°	603827
15°	476480
20°	317810
25°	182922
30°	92674
35°	43409
40°	17748
45°	8053
50°	4098
55°	2634
60°	1472
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224603

CATALOG NUMBER: LSR2B15FL409030D2WD010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	21.0
10°-20°	321.1	42.2
20°-30°	201.1	26.4
30°-40°	62.2	8.2
40°-50°	12.9	1.7
50°-60°	3.6	0.5
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.2	89.6
0°-40°	744.4	97.8
0°-60°	760.9	99.9
0°-90°	761.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1789	
5°	1748	160
15°	1188	321
25°	428	201
35°	92	62
45°	15	13
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224603

CATALOG NUMBER: LSR2B15FL409030D2WD010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1789.3
2.5°	1780.5
5°	1748.2
7.5°	1666.1
10°	1535.2
12.5°	1374.0
15°	1188.2
17.5°	974.3
20°	771.0
22.5°	586.3
25°	428.0
27.5°	301.0
30°	207.2
32.5°	138.7
35°	91.8
37.5°	57.6
40°	35.1
42.5°	22.5
45°	14.7
47.5°	9.8
50°	6.8
52.5°	4.9
55°	3.9
57.5°	3.0
60°	1.9
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)