

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222750

Luminaire Tested: **LSRWM2B15NFL259030D2WD010 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B15NFL259030D2WD010 2LBDL*WH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 768.0 lumens
Efficiency: N/A
Efficacy: 53.7 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222750

CATALOG NUMBER: LSRWM2B15NFL259030D2WD010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P222750

CATALOG NUMBER: LSRWM2B15NFL259030D2WD010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97																																				
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95																																				
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92																																				
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90																																				
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88																																				
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86																																				
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84																																				
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82																																				
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80																																				
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1764942
5°	1629607
10°	1103031
15°	375265
20°	137841
25°	73084
30°	37571
35°	17543
40°	5714
45°	2903
50°	1386
55°	473
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222750

CATALOG NUMBER: LSRWM2B15NFL259030D2WD010 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	356.5	46.4
10°-20°	299.8	39.0
20°-30°	82.3	10.7
30°-40°	24.0	3.1
40°-50°	4.4	0.6
50°-60°	1.0	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	738.5	96.2
0°-40°	762.5	99.3
0°-60°	767.9	100.0
0°-90°	768.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	768.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4556	
5°	4191	357
15°	936	300
25°	171	82
35°	37	24
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222750

CATALOG NUMBER: LSRWM2B15NFL259030D2WD010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4556.5
1°	4530.1
2°	4483.1
3°	4415.8
4°	4323.5
5°	4191.1
6°	4010.3
7°	3784.1
8°	3508.0
9°	3181.9
10°	2804.4
11°	2390.6
12°	1960.1
13°	1549.3
14°	1199.1
15°	935.8
17.5°	528.1
20°	334.4
22.5°	238.3
25°	171.0
27.5°	121.1
30°	84.0
32.5°	59.0
35°	37.1
37.5°	15.1
40°	11.3
42.5°	8.3
45°	5.3
47.5°	3.0
50°	2.3
52.5°	1.5
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222750

CATALOG NUMBER: LSRWM2B15NFL259030D2WD010 2LBDL*WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)