

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222853

Luminaire Tested: **LSSQ2B15NFL259027D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222853
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B15NFL259027D010 2LBDLC*MB
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 982.3 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222853

CATALOG NUMBER: LSSQ2B15NFL259027D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P222853

CATALOG NUMBER: LSSQ2B15NFL259027D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	93	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	88
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	86
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	84
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	83	82	82
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	80
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	79	79
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2257297
5°	2084222
10°	1410726
15°	479969
20°	176300
25°	93470
30°	48037
35°	22414
40°	7332
45°	3725
50°	1748
55°	675
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222853

CATALOG NUMBER: LSSQ2B15NFL259027D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	456.0	46.4
10°-20°	383.4	39.0
20°-30°	105.2	10.7
30°-40°	30.7	3.1
40°-50°	5.7	0.6
50°-60°	1.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	944.6	96.2
0°-40°	975.2	99.3
0°-60°	982.2	100.0
0°-90°	982.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	982.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5828	
5°	5360	456
15°	1197	383
25°	219	105
35°	47	31
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222853

CATALOG NUMBER: LSSQ2B15NFL259027D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	5827.6
1°	5793.8
2°	5733.8
3°	5647.6
4°	5529.6
5°	5360.3
6°	5129.0
7°	4839.7
8°	4486.6
9°	4069.6
10°	3586.7
11°	3057.5
12°	2506.9
13°	1981.6
14°	1533.6
15°	1196.9
17.5°	675.4
20°	427.7
22.5°	304.8
25°	218.7
27.5°	154.8
30°	107.4
32.5°	75.5
35°	47.4
37.5°	19.4
40°	14.5
42.5°	10.6
45°	6.8
47.5°	3.9
50°	2.9
52.5°	1.9
55°	1.0
57.5°	1.0
60°	1.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222853

CATALOG NUMBER: LSSQ2B15NFL259027D010 2LBDLC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)