

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224919

Luminaire Tested: **LSSQWM2B15FL409027D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409027D010 2LBD*H
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1063.2 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224919

CATALOG NUMBER: LSSQWM2B15FL409027D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224919

CATALOG NUMBER: LSSQWM2B15FL409027D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95															
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91				91															
3	106	100	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87				87															
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83				83															
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79				79															
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76				76															
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73				73															
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70				70															
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67				67															
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64				64															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	986067
5°	965415
10°	850243
15°	667080
20°	442997
25°	254296
30°	127516
35°	58919
40°	23968
45°	10737
50°	5604
55°	3444
60°	1627
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224919

CATALOG NUMBER: LSSQWM2B15FL409027D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.8	21.3
10°-20°	450.3	42.4
20°-30°	279.8	26.3
30°-40°	84.4	7.9
40°-50°	17.3	1.6
50°-60°	4.4	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	956.8	90.0
0°-40°	1041.2	97.9
0°-60°	1062.9	100.0
0°-90°	1063.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1063.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2546	
5°	2483	227
15°	1664	450
25°	595	280
35°	125	84
45°	20	17
55°	5	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224919

CATALOG NUMBER: LSSQWM2B15FL409027D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2545.7
1°	2537.5
2°	2526.1
3°	2517.9
4°	2505.6
5°	2482.9
6°	2446.9
7°	2397.5
8°	2326.4
9°	2246.1
10°	2161.7
11°	2072.2
12°	1978.5
13°	1880.7
14°	1773.7
15°	1663.5
17.5°	1368.1
20°	1074.7
22.5°	815.3
25°	595.0
27.5°	420.0
30°	285.1
32.5°	187.4
35°	124.6
37.5°	77.2
40°	47.4
42.5°	30.9
45°	19.6
47.5°	12.4
50°	9.3
52.5°	6.2
55°	5.1
57.5°	3.1
60°	2.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224919

CATALOG NUMBER: LSSQWM2B15FL409027D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)