

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225492

Luminaire Tested: **LSSQWM2B15FL409727D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225492
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14832)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409727D010 2LBDL*H
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 897.9 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225492

CATALOG NUMBER: LSSQWM2B15FL409727D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P225492

CATALOG NUMBER: LSSQWM2B15FL409727D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																												
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90																												
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86																												
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82																												
5	97	90	85	81	96	89	84	81	87	83	80	86	82	80	84	81	79	78																												
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74																												
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	75	72	71																												
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68																												
9	83	75	70	67	82	75	70	67	74	69	66	73	69	66	72	69	66	65																												
10	80	72	67	64	79	72	67	64	71	67	64	70	66	64	70	66	63	62																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	789295
5°	763031
10°	673248
15°	530376
20°	364472
25°	220105
30°	119331
35°	61330
40°	29985
45°	14188
50°	7412
55°	4997
60°	2866
65°	1100
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225492

CATALOG NUMBER: LSSQWM2B15FL409727D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.3	20.0
10°-20°	360.1	40.1
20°-30°	240.6	26.8
30°-40°	87.1	9.7
40°-50°	22.5	2.5
50°-60°	6.7	0.7
60°-70°	1.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	779.9	86.9
0°-40°	867.1	96.6
0°-60°	896.2	99.8
0°-90°	897.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	897.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2038	
5°	1962	179
15°	1323	360
25°	515	241
35°	130	87
45°	26	22
55°	7	7
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225492

CATALOG NUMBER: LSSQWM2B15FL409727D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2037.7
2.5°	2019.2
5°	1962.4
7.5°	1858.6
10°	1711.7
12.5°	1531.4
15°	1322.6
17.5°	1100.4
20°	884.2
22.5°	685.4
25°	515.0
27.5°	375.4
30°	266.8
32.5°	187.7
35°	129.7
37.5°	90.2
40°	59.3
42.5°	38.3
45°	25.9
47.5°	18.5
50°	12.3
52.5°	9.9
55°	7.4
57.5°	4.9
60°	3.7
62.5°	2.5
65°	1.2
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)