

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B15WFL559030D2WD010 2LBDL\*GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14806)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B15WFL559030D2WD010 2LBDL\*GPH  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 702.9 lumens  
Efficiency: N/A  
Efficacy: 49.2 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL559030D2WD010 2LBDL\*GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL559030D2WD010 2LBDL\*GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 93  |    |    |   |
| 2   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 92  | 95  | 92  | 90  | 92  | 90  | 88  | 86  |    |    |   |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 86  | 91  | 88  | 84  | 89  | 86  | 83  | 87  | 84  | 82  | 80  |    |    |   |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 74  |    |    |   |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 72  | 80  | 75  | 72  | 79  | 74  | 71  | 77  | 73  | 70  | 69  |    |    |   |
| 6   | 87  | 78  | 72  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 67  | 74  | 70  | 66  | 73  | 69  | 66  | 64  |    |    |   |
| 7   | 83  | 73  | 67  | 63  | 81  | 72  | 67  | 62  | 71  | 66  | 62  | 70  | 65  | 62  | 69  | 65  | 61  | 60  |    |    |   |
| 8   | 78  | 69  | 63  | 58  | 77  | 68  | 62  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 58  | 56  |    |    |   |
| 9   | 75  | 65  | 59  | 55  | 74  | 64  | 59  | 55  | 63  | 58  | 54  | 62  | 58  | 54  | 62  | 57  | 54  | 53  |    |    |   |
| 10  | 71  | 61  | 55  | 51  | 70  | 61  | 55  | 51  | 60  | 55  | 51  | 59  | 54  | 51  | 58  | 54  | 51  | 50  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 334938 |
| 5°  | 331279 |
| 10° | 306161 |
| 15° | 268115 |
| 20° | 231165 |
| 25° | 197326 |
| 30° | 156097 |
| 35° | 108002 |
| 40° | 69880  |
| 45° | 42454  |
| 50° | 24767  |
| 55° | 13912  |
| 60° | 5345   |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL559030D2WD010 2LBDL\*GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 78.9   | 11.2      |
| 10°-20°   | 186.4  | 26.5      |
| 20°-30°   | 209.7  | 29.8      |
| 30°-40°   | 144.7  | 20.6      |
| 40°-50°   | 62.5   | 8.9       |
| 50°-60°   | 19.4   | 2.8       |
| 60°-70°   | 1.3    | 0.2       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 475.1  | 67.6      |
| 0°-40°    | 619.8  | 88.2      |
| 0°-60°    | 701.6  | 99.8      |
| 0°-90°    | 702.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 702.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 865 |      |
| 5°  | 852 | 79   |
| 15° | 669 | 186  |
| 25° | 462 | 210  |
| 35° | 228 | 145  |
| 45° | 78  | 62   |
| 55° | 21  | 19   |
| 65° | 0   | 1    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL559030D2WD010 2LBDL\*GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 864.7 |
| 2.5°  | 862.7 |
| 5°    | 852.0 |
| 7.5°  | 823.5 |
| 10°   | 778.4 |
| 12.5° | 725.4 |
| 15°   | 668.6 |
| 17.5° | 611.8 |
| 20°   | 560.8 |
| 22.5° | 511.7 |
| 25°   | 461.7 |
| 27.5° | 408.8 |
| 30°   | 349.0 |
| 32.5° | 286.3 |
| 35°   | 228.4 |
| 37.5° | 179.4 |
| 40°   | 138.2 |
| 42.5° | 103.9 |
| 45°   | 77.5  |
| 47.5° | 56.8  |
| 50°   | 41.1  |
| 52.5° | 29.4  |
| 55°   | 20.6  |
| 57.5° | 13.7  |
| 60°   | 6.9   |
| 62.5° | 1.9   |
| 65°   | 0.0   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)