

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224694

Luminaire Tested: **LSR2B15FL408030D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15FL408030D010 2LBDLC*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1276.8 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224694

CATALOG NUMBER: LSR2B15FL408030D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224694

CATALOG NUMBER: LSR2B15FL408030D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79	79	79	79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1155918
5°	1134826
10°	1008830
15°	793398
20°	527952
25°	303104
30°	153100
35°	72017
40°	28973
45°	14352
50°	7894
55°	5538
60°	5113
65°	3025
70°	3737
75°	2395
80°	3569
85°	0



TEST NUMBER: P224694

CATALOG NUMBER: LSR2B15FL408030D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.3	20.9
10°-20°	535.9	42.0
20°-30°	333.4	26.1
30°-40°	102.5	8.0
40°-50°	22.5	1.8
50°-60°	8.0	0.6
60°-70°	4.1	0.3
70°-80°	2.4	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1136.6	89.0
0°-40°	1239.1	97.1
0°-60°	1269.7	99.4
0°-90°	1276.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1276.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2984	
5°	2919	267
15°	1978	536
25°	709	333
35°	152	102
45°	26	23
55°	8	8
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P224694

CATALOG NUMBER: LSR2B15FL408030D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2984.2
2.5°	2971.1
5°	2918.6
7.5°	2786.0
10°	2564.9
12.5°	2299.5
15°	1978.5
17.5°	1628.0
20°	1280.8
22.5°	971.2
25°	709.2
27.5°	499.5
30°	342.3
32.5°	230.9
35°	152.3
37.5°	91.7
40°	57.3
42.5°	39.3
45°	26.2
47.5°	18.0
50°	13.1
52.5°	11.5
55°	8.2
57.5°	6.6
60°	6.6
62.5°	4.9
65°	3.3
67.5°	3.3
70°	3.3
72.5°	3.3
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)