

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B15WFL558030D010 2LBDL*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14806)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15WFL558030D010 2LBDL*GPH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1176.3 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B15WFL558030D010 2LBDL*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558030D010 2LBDL*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																											
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																											
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																											
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74																											
5	92	83	77	73	90	82	77	72	80	75	72	79	74	71	77	73	70	69																											
6	87	78	72	67	85	77	71	67	75	70	67	74	70	66	73	69	66	64																											
7	83	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60																											
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56																											
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53																											
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	560490
5°	554310
10°	512340
15°	448650
20°	386813
25°	330243
30°	261205
35°	180728
40°	116956
45°	70994
50°	41519
55°	23298
60°	8909
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558030D010 2LBDL*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.1	11.2
10°-20°	311.9	26.5
20°-30°	351.0	29.8
30°-40°	242.1	20.6
40°-50°	104.6	8.9
50°-60°	32.5	2.8
60°-70°	2.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	795.0	67.6
0°-40°	1037.1	88.2
0°-60°	1174.1	99.8
0°-90°	1176.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1176.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1447	
5°	1426	132
15°	1119	312
25°	773	351
35°	382	242
45°	130	105
55°	34	32
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558030D010 2LBDL*GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1447.0
2.5°	1443.7
5°	1425.6
7.5°	1378.1
10°	1302.6
12.5°	1214.0
15°	1118.8
17.5°	1023.7
20°	938.4
22.5°	856.4
25°	772.7
27.5°	684.1
30°	584.0
32.5°	479.0
35°	382.2
37.5°	300.2
40°	231.3
42.5°	173.9
45°	129.6
47.5°	95.2
50°	68.9
52.5°	49.2
55°	34.5
57.5°	23.0
60°	11.5
62.5°	3.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)