

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225409

Luminaire Tested: **LSSQWM2B20FL409024D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL409024D010 2LBDC*MB
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1322.8 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225409

CATALOG NUMBER: LSSQWM2B20FL409024D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225409

CATALOG NUMBER: LSSQWM2B20FL409024D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	96	94	92	91				91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87				87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83				83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79				79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76				76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72				72
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69				69
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67				67
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1196860
5°	1176042
10°	1049146
15°	829249
20°	552932
25°	320798
30°	160569
35°	75516
40°	29530
45°	13147
50°	6207
55°	3512
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225409

CATALOG NUMBER: LSSQWM2B20FL409024D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.2	21.0
10°-20°	559.7	42.3
20°-30°	352.1	26.6
30°-40°	107.6	8.1
40°-50°	21.1	1.6
50°-60°	4.8	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1189.1	89.9
0°-40°	1296.7	98.0
0°-60°	1322.6	100.0
0°-90°	1322.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1322.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3090	
5°	3025	277
15°	2068	560
25°	751	352
35°	160	108
45°	24	21
55°	5	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225409

CATALOG NUMBER: LSSQWM2B20FL409024D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3089.9
2.5°	3083.0
5°	3024.6
7.5°	2887.2
10°	2667.4
12.5°	2392.6
15°	2067.9
17.5°	1707.3
20°	1341.4
22.5°	1028.8
25°	750.6
27.5°	529.0
30°	359.0
32.5°	242.2
35°	159.7
37.5°	97.9
40°	58.4
42.5°	37.8
45°	24.0
47.5°	15.5
50°	10.3
52.5°	6.9
55°	5.2
57.5°	3.4
60°	1.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)