

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225107

Luminaire Tested: **LSR2WM2B20FL408027D010 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14829)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408027D010 2LBD*WH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1855.7 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225107

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P225107

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	100	108	104	101	98		101	98	96			98	96	94			95
3	106	100	96	93	104	99	95	92		96	93	91			94	91	89			92
4	102	95	91	87	100	94	90	87		92	89	86			90	87	85			88
5	98	91	86	82	96	90	85	82		88	84	81			87	83	81			85
6	94	87	82	78	93	86	81	78		85	80	77			83	80	77			82
7	90	83	78	75	89	82	78	74		81	77	74			80	76	74			79
8	87	79	75	71	86	79	74	71		78	74	71			77	73	70			76
9	84	76	71	68	83	76	71	68		75	71	68			74	70	68			73
10	81	73	69	65	80	73	68	65		72	68	65			71	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1712185
5°	1647415
10°	1450058
15°	1138989
20°	774368
25°	452220
30°	230299
35°	108947
40°	47531
45°	20597
50°	9943
55°	6348
60°	3641
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225107

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.0	20.9
10°-20°	772.3	41.6
20°-30°	495.8	26.7
30°-40°	157.3	8.5
40°-50°	33.6	1.8
50°-60°	8.6	0.5
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1655.1	89.2
0°-40°	1812.3	97.7
0°-60°	1854.6	99.9
0°-90°	1855.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1855.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4420	
5°	4237	387
15°	2840	772
25°	1058	496
35°	230	157
45°	38	34
55°	9	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225107

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBD*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4420.3
2.5°	4378.0
5°	4236.9
7.5°	4006.5
10°	3686.7
12.5°	3296.4
15°	2840.3
17.5°	2353.6
20°	1878.6
22.5°	1434.2
25°	1058.1
27.5°	754.7
30°	514.9
32.5°	345.6
35°	230.4
37.5°	152.8
40°	94.0
42.5°	58.8
45°	37.6
47.5°	25.9
50°	16.5
52.5°	11.8
55°	9.4
57.5°	7.1
60°	4.7
62.5°	2.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)