

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223486

Luminaire Tested: **LSR2WM2B20NFL258027D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223486
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20NFL258027D010 2LBDLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1681.3 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223486

CATALOG NUMBER: LSR2WM2B20NFL258027D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P223486

CATALOG NUMBER: LSR2WM2B20NFL258027D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	115	113	112	110	113	111	110	108		107	106	105			104	103	102			97
2	112	109	106	104	110	107	104	102		104	102	100			101	99	98			95
3	109	105	101	99	107	103	100	98		101	98	96			99	97	95			92
4	106	101	97	95	104	100	97	94		98	95	93			96	94	92			90
5	103	98	94	91	102	97	94	91		95	92	90			94	91	89			88
6	101	95	91	89	99	94	91	88		93	90	88			92	89	87			86
7	98	92	89	86	97	92	88	86		91	88	85			90	87	85			84
8	96	90	86	84	95	90	86	84		89	86	83			88	85	83			82
9	94	88	84	82	93	88	84	82		87	84	82			86	83	81			80
10	92	86	82	80	91	86	82	80		85	82	80			84	82	80			79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3863583
5°	3567319
10°	2414640
15°	821509
20°	301734
25°	159972
30°	82208
35°	38349
40°	12540
45°	6354
50°	3013
55°	1148
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223486

CATALOG NUMBER: LSR2WM2B20NFL258027D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	780.4	46.4
10°-20°	656.2	39.0
20°-30°	180.1	10.7
30°-40°	52.5	3.1
40°-50°	9.7	0.6
50°-60°	2.2	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1616.7	96.2
0°-40°	1669.2	99.3
0°-60°	1681.1	100.0
0°-90°	1681.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1681.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9974	
5°	9175	780
15°	2049	656
25°	374	180
35°	81	52
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223486

CATALOG NUMBER: LSR2WM2B20NFL258027D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	9974.5
1°	9916.6
2°	9813.9
3°	9666.5
4°	9464.4
5°	9174.6
6°	8778.8
7°	8283.7
8°	7679.2
9°	6965.4
10°	6139.1
11°	5233.2
12°	4290.9
13°	3391.6
14°	2624.9
15°	2048.6
17.5°	1155.9
20°	732.0
22.5°	521.7
25°	374.3
27.5°	265.0
30°	183.8
32.5°	129.2
35°	81.1
37.5°	33.1
40°	24.8
42.5°	18.2
45°	11.6
47.5°	6.6
50°	5.0
52.5°	3.3
55°	1.7
57.5°	1.7
60°	1.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223486

CATALOG NUMBER: LSR2WM2B20NFL258027D010 2LBDLC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)