

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223374

Luminaire Tested: **LSSQWM2B15NFL258030D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223374
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15NFL258030D010 2LBDL*LI
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1287.6 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223374

CATALOG NUMBER: LSSQWM2B15NFL258030D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P223374

CATALOG NUMBER: LSSQWM2B15NFL258030D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	95	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	92	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	90	90	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	88	88	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	86	86	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	84	84	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	82	82	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	80	80	80
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2958859
5°	2732005
10°	1849201
15°	629145
20°	231082
25°	122490
30°	62975
35°	29365
40°	9607
45°	4875
50°	2290
55°	878
60°	1007
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223374

CATALOG NUMBER: LSSQWM2B15NFL258030D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	597.7	46.4
10°-20°	502.5	39.0
20°-30°	137.9	10.7
30°-40°	40.2	3.1
40°-50°	7.5	0.6
50°-60°	1.7	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1238.1	96.2
0°-40°	1278.3	99.3
0°-60°	1287.5	100.0
0°-90°	1287.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1287.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7639	
5°	7026	598
15°	1569	503
25°	287	138
35°	62	40
45°	9	7
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223374

CATALOG NUMBER: LSSQWM2B15NFL258030D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7638.8
1°	7594.5
2°	7515.8
3°	7402.9
4°	7248.2
5°	7026.3
6°	6723.1
7°	6343.9
8°	5881.0
9°	5334.4
10°	4701.5
11°	4007.8
12°	3286.1
13°	2597.4
14°	2010.2
15°	1568.9
17.5°	885.3
20°	560.6
22.5°	399.5
25°	286.6
27.5°	202.9
30°	140.8
32.5°	98.9
35°	62.1
37.5°	25.4
40°	19.0
42.5°	14.0
45°	8.9
47.5°	5.1
50°	3.8
52.5°	2.5
55°	1.3
57.5°	1.3
60°	1.3
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223374

CATALOG NUMBER: LSSQWM2B15NFL258030D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)