

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222742

Luminaire Tested: **LSR2B15NFL259030D010 2LBDC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P222742  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B15NFL259030D010 2LBDC\*MB  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
NARROW FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1088.3 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P222742

CATALOG NUMBER: LSR2B15NFL259030D010 2LBDC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P222742

CATALOG NUMBER: LSR2B15NFL259030D010 2LBDC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97									97																		
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95									95																		
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92									92																		
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90									90																		
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88									88																		
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86									86																		
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84									84																		
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82									82																		
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80									80																		
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79									79																		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2500899
5°	2309119
10°	1562981
15°	531739
20°	195303
25°	103556
30°	53225
35°	24825
40°	8141
45°	4108
50°	1928
55°	743
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222742

CATALOG NUMBER: LSR2B15NFL259030D010 2LBDC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	505.2	46.4
10°-20°	424.7	39.0
20°-30°	116.6	10.7
30°-40°	34.0	3.1
40°-50°	6.3	0.6
50°-60°	1.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.5	96.2
0°-40°	1080.4	99.3
0°-60°	1088.2	100.0
0°-90°	1088.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1088.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6456	
5°	5939	505
15°	1326	425
25°	242	117
35°	52	34
45°	8	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222742

CATALOG NUMBER: LSR2B15NFL259030D010 2LBDC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6456.5
1°	6419.0
2°	6352.5
3°	6257.1
4°	6126.3
5°	5938.7
6°	5682.5
7°	5362.0
8°	4970.7
9°	4508.7
10°	3973.8
11°	3387.4
12°	2777.5
13°	2195.4
14°	1699.1
15°	1326.0
17.5°	748.2
20°	473.8
22.5°	337.7
25°	242.3
27.5°	171.5
30°	119.0
32.5°	83.6
35°	52.5
37.5°	21.4
40°	16.1
42.5°	11.8
45°	7.5
47.5°	4.3
50°	3.2
52.5°	2.1
55°	1.1
57.5°	1.1
60°	1.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222742

CATALOG NUMBER: LSR2B15NFL259030D010 2LBDC\*MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)