

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2WM2B20WFL559027D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20WFL559027D010 2LBDLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1225.8 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL559027D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL559027D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	110	108	106		111	108	106	104		104	102	101			101	99	98			97
2	108	102	98	95		105	101	97	94		98	94	92			95	92	90			92
3	102	95	90	86		100	94	89	85		91	87	84			89	85	83			87
4	97	89	83	79		95	88	82	78		85	81	77			83	80	76			82
5	91	83	77	72		90	82	76	72		80	75	71			78	74	71			77
6	87	78	71	67		85	77	71	67		75	70	66			74	69	66			73
7	82	73	67	62		81	72	66	62		71	66	62			70	65	62			69
8	78	69	62	58		77	68	62	58		67	62	58			66	61	58			65
9	74	65	59	55		73	64	58	54		63	58	54			62	57	54			61
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	575015
5°	571340
10°	531141
15°	466295
20°	401941
25°	343706
30°	272789
35°	190138
40°	120293
45°	73404
50°	43387
55°	23771
60°	5190
65°	4583
70°	3851
75°	5088
80°	3792
85°	7555



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL559027D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.4	11.1
10°-20°	323.8	26.4
20°-30°	365.4	29.8
30°-40°	252.8	20.6
40°-50°	107.7	8.8
50°-60°	31.2	2.5
60°-70°	4.6	0.4
70°-80°	2.9	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	825.6	67.3
0°-40°	1078.3	88.0
0°-60°	1217.2	99.3
0°-90°	1225.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1225.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1484	
5°	1469	136
15°	1163	324
25°	804	365
35°	402	253
45°	134	108
55°	35	31
65°	5	5
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL559027D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1484.5
2.5°	1482.8
5°	1469.4
7.5°	1424.2
10°	1350.4
12.5°	1260.0
15°	1162.8
17.5°	1062.3
20°	975.1
22.5°	893.0
25°	804.2
27.5°	710.4
30°	609.9
32.5°	501.0
35°	402.1
37.5°	311.6
40°	237.9
42.5°	179.3
45°	134.0
47.5°	97.2
50°	72.0
52.5°	51.9
55°	35.2
57.5°	15.1
60°	6.7
62.5°	5.0
65°	5.0
67.5°	3.4
70°	3.4
72.5°	3.4
75°	3.4
77.5°	1.7
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)