

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224927

Luminaire Tested: **LSSQWM2B20FL409027D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224927
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL409027D010 2LBD*H
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1434.2 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224927

CATALOG NUMBER: LSSQWM2B20FL409027D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224927

CATALOG NUMBER: LSSQWM2B20FL409027D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	103	100		108	104	101	99		101	99	97			98	96	94			96
3	106	100	96	93		104	99	95	92		97	94	91			94	92	90			92
4	102	96	91	88		100	94	90	87		92	89	86			91	88	85			89
5	98	91	86	83		96	90	86	82		89	85	82			87	84	81			86
6	94	87	82	79		93	86	82	78		85	81	78			84	80	77			82
7	91	83	78	75		90	83	78	75		82	77	74			80	77	74			79
8	88	80	75	72		87	79	75	72		78	74	71			77	74	71			77
9	85	77	72	69		84	76	72	69		75	71	68			75	71	68			74
10	82	74	69	66		81	73	69	66		73	69	66			72	68	66			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1330262
5°	1302410
10°	1147043
15°	899947
20°	597615
25°	343065
30°	172064
35°	79441
40°	32311
45°	14462
50°	7533
55°	4660
60°	2169
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224927

CATALOG NUMBER: LSSQWM2B20FL409027D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.9	21.3
10°-20°	607.4	42.4
20°-30°	377.4	26.3
30°-40°	113.8	7.9
40°-50°	23.3	1.6
50°-60°	6.0	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1290.8	90.0
0°-40°	1404.6	97.9
0°-60°	1433.9	100.0
0°-90°	1434.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1434.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3434	
5°	3350	306
15°	2244	607
25°	803	377
35°	168	114
45°	26	23
55°	7	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224927

CATALOG NUMBER: LSSQWM2B20FL409027D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3434.3
1°	3423.2
2°	3408.0
3°	3396.8
4°	3380.2
5°	3349.6
6°	3301.0
7°	3234.4
8°	3138.5
9°	3030.2
10°	2916.3
11°	2795.5
12°	2669.1
13°	2537.2
14°	2392.8
15°	2244.2
17.5°	1845.6
20°	1449.8
22.5°	1099.9
25°	802.7
27.5°	566.6
30°	384.7
32.5°	252.7
35°	168.0
37.5°	104.2
40°	63.9
42.5°	41.7
45°	26.4
47.5°	16.7
50°	12.5
52.5°	8.3
55°	6.9
57.5°	4.2
60°	2.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224927

CATALOG NUMBER: LSSQWM2B20FL409027D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)