

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224979

Luminaire Tested: **LSSQWM2B15FL409030D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224979
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409030D010 2LBDL*LI
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1048.8 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224979

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224979

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76	76	76	76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73	73	73	73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70	70	70	70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67	67	67	67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65	65	65	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1006054
5°	966815
10°	841629
15°	657175
20°	437061
25°	250279
30°	124430
35°	57169
40°	22956
45°	10463
50°	4881
55°	2701
60°	1549
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224979

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.3	21.6
10°-20°	444.4	42.4
20°-30°	275.0	26.2
30°-40°	82.3	7.8
40°-50°	16.5	1.6
50°-60°	4.0	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	945.7	90.2
0°-40°	1028.0	98.0
0°-60°	1048.5	100.0
0°-90°	1048.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1048.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2597	
5°	2486	226
15°	1639	444
25°	586	275
35°	121	82
45°	19	16
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224979

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2597.3
1°	2583.2
2°	2570.1
3°	2543.9
4°	2519.7
5°	2486.5
6°	2441.1
7°	2383.7
8°	2310.1
9°	2226.4
10°	2139.8
11°	2050.1
12°	1954.3
13°	1854.5
14°	1747.7
15°	1638.8
17.5°	1351.6
20°	1060.3
22.5°	802.3
25°	585.6
27.5°	411.2
30°	278.2
32.5°	183.4
35°	120.9
37.5°	75.6
40°	45.4
42.5°	29.2
45°	19.1
47.5°	12.1
50°	8.1
52.5°	6.0
55°	4.0
57.5°	3.0
60°	2.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224979

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)