

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224671

Luminaire Tested: **LSSQWM2B15FL409030D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224671
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409030D010 2LBDLC*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1030.7 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224671

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224671

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	933194
5°	916190
10°	814451
15°	640533
20°	426220
25°	244680
30°	123625
35°	58162
40°	23411
45°	11613
50°	6388
55°	4457
60°	4106
65°	2383
70°	2945
75°	1946
80°	2900
85°	0



TEST NUMBER: P224671

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.8	20.9
10°-20°	432.7	42.0
20°-30°	269.2	26.1
30°-40°	82.8	8.0
40°-50°	18.2	1.8
50°-60°	6.5	0.6
60°-70°	3.2	0.3
70°-80°	1.9	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	917.7	89.0
0°-40°	1000.4	97.1
0°-60°	1025.1	99.5
0°-90°	1030.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1030.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2409	
5°	2356	216
15°	1597	433
25°	572	269
35°	123	83
45°	21	18
55°	7	6
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P224671

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2409.2
2.5°	2398.6
5°	2356.3
7.5°	2249.2
10°	2070.7
12.5°	1856.5
15°	1597.3
17.5°	1314.4
20°	1034.0
22.5°	784.1
25°	572.5
27.5°	403.3
30°	276.4
32.5°	186.4
35°	123.0
37.5°	74.0
40°	46.3
42.5°	31.7
45°	21.2
47.5°	14.5
50°	10.6
52.5°	9.3
55°	6.6
57.5°	5.3
60°	5.3
62.5°	4.0
65°	2.6
67.5°	2.6
70°	2.6
72.5°	2.6
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)