

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222352

Luminaire Tested: **LSR2B20NFL259727D010 2LBDLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P222352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B20NFL259727D010 2LBDLC\*MB  
Description: 2000 Lumen, 2inch Portfolio LED Cylinder  
NARROW FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1191.9 lumens  
Efficiency: N/A  
Efficacy: 57.0 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P222352

CATALOG NUMBER: LSR2B20NFL259727D010 2LBDLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P222352

CATALOG NUMBER: LSR2B20NFL259727D010 2LBDLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 |
| 1   | 115 | 113 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 100 | 99  | 97  | 97  | 97  |
| 2   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 95  | 95  | 95  |
| 3   | 109 | 105 | 101 | 99  | 107 | 103 | 100 | 98  | 101 | 98  | 96  | 99  | 97  | 95  | 96  | 95  | 93  | 92  | 92  | 92  |
| 4   | 106 | 101 | 97  | 95  | 104 | 100 | 97  | 94  | 98  | 95  | 93  | 96  | 94  | 92  | 95  | 93  | 91  | 90  | 90  | 90  |
| 5   | 103 | 98  | 94  | 91  | 102 | 97  | 94  | 91  | 95  | 92  | 90  | 94  | 91  | 89  | 93  | 90  | 89  | 88  | 88  | 88  |
| 6   | 101 | 95  | 91  | 89  | 99  | 94  | 91  | 88  | 93  | 90  | 88  | 92  | 89  | 87  | 91  | 88  | 87  | 86  | 86  | 86  |
| 7   | 98  | 92  | 89  | 86  | 97  | 92  | 88  | 86  | 91  | 88  | 85  | 90  | 87  | 85  | 89  | 86  | 85  | 84  | 84  | 84  |
| 8   | 96  | 90  | 86  | 84  | 95  | 90  | 86  | 84  | 89  | 86  | 83  | 88  | 85  | 83  | 87  | 85  | 83  | 82  | 82  | 82  |
| 9   | 94  | 88  | 84  | 82  | 93  | 88  | 84  | 82  | 87  | 84  | 82  | 86  | 83  | 81  | 85  | 83  | 81  | 80  | 80  | 80  |
| 10  | 92  | 86  | 82  | 80  | 91  | 86  | 82  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 84  | 81  | 79  | 79  | 79  | 79  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2738962 |
| 5°  | 2528922 |
| 10° | 1711774 |
| 15° | 582387  |
| 20° | 213893  |
| 25° | 113386  |
| 30° | 58279   |
| 35° | 27190   |
| 40° | 8899    |
| 45° | 4492    |
| 50° | 2109    |
| 55° | 810     |
| 60° | 930     |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P222352

CATALOG NUMBER: LSR2B20NFL259727D010 2LBDLC\*MB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 553.3  | 46.4      |
| 10°-20°   | 465.2  | 39.0      |
| 20°-30°   | 127.6  | 10.7      |
| 30°-40°   | 37.2   | 3.1       |
| 40°-50°   | 6.9    | 0.6       |
| 50°-60°   | 1.6    | 0.1       |
| 60°-70°   | 0.1    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1146.1 | 96.2      |
| 0°-40°    | 1183.3 | 99.3      |
| 0°-60°    | 1191.7 | 100.0     |
| 0°-90°    | 1191.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1191.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 7071 |      |
| 5°  | 6504 | 553  |
| 15° | 1452 | 465  |
| 25° | 265  | 128  |
| 35° | 58   | 37   |
| 45° | 8    | 7    |
| 55° | 1    | 2    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P222352

CATALOG NUMBER: LSR2B20NFL259727D010 2LBDLC\*MB

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 7071.1 |
| 1°    | 7030.0 |
| 2°    | 6957.2 |
| 3°    | 6852.7 |
| 4°    | 6709.5 |
| 5°    | 6504.0 |
| 6°    | 6223.5 |
| 7°    | 5872.4 |
| 8°    | 5443.9 |
| 9°    | 4937.9 |
| 10°   | 4352.1 |
| 11°   | 3709.9 |
| 12°   | 3041.9 |
| 13°   | 2404.4 |
| 14°   | 1860.8 |
| 15°   | 1452.3 |
| 17.5° | 819.5  |
| 20°   | 518.9  |
| 22.5° | 369.8  |
| 25°   | 265.3  |
| 27.5° | 187.8  |
| 30°   | 130.3  |
| 32.5° | 91.6   |
| 35°   | 57.5   |
| 37.5° | 23.5   |
| 40°   | 17.6   |
| 42.5° | 12.9   |
| 45°   | 8.2    |
| 47.5° | 4.7    |
| 50°   | 3.5    |
| 52.5° | 2.3    |
| 55°   | 1.2    |
| 57.5° | 1.2    |
| 60°   | 1.2    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P222352

CATALOG NUMBER: LSR2B20NFL259727D010 2LBDLC\*MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







|       |     |
|-------|-----|
| 85°   | 0.0 |
| 87.5° | 0.0 |



(END OF REPORT)