

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222247

Luminaire Tested: **LSR2B15NFL259730D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15NFL259730D010 2LBDLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 948.2 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222247

CATALOG NUMBER: LSR2B15NFL259730D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P222247

CATALOG NUMBER: LSR2B15NFL259730D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97																												
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95																												
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92																												
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90																												
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88																												
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86																												
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84																												
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82																												
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80																												
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2178937
5°	2011861
10°	1361757
15°	463287
20°	170158
25°	90222
30°	46382
35°	21657
40°	7079
45°	3561
50°	1687
55°	608
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222247

CATALOG NUMBER: LSR2B15NFL259730D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	440.1	46.4
10°-20°	370.1	39.0
20°-30°	101.6	10.7
30°-40°	29.6	3.1
40°-50°	5.5	0.6
50°-60°	1.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	911.8	96.2
0°-40°	941.4	99.3
0°-60°	948.1	100.0
0°-90°	948.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	948.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5625	
5°	5174	440
15°	1155	370
25°	211	102
35°	46	30
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222247

CATALOG NUMBER: LSR2B15NFL259730D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5625.3
1°	5592.6
2°	5534.7
3°	5451.6
4°	5337.6
5°	5174.2
6°	4951.0
7°	4671.7
8°	4330.8
9°	3928.3
10°	3462.2
11°	2951.4
12°	2419.9
13°	1912.8
14°	1480.3
15°	1155.3
17.5°	651.9
20°	412.8
22.5°	294.2
25°	211.1
27.5°	149.4
30°	103.7
32.5°	72.8
35°	45.8
37.5°	18.7
40°	14.0
42.5°	10.3
45°	6.5
47.5°	3.7
50°	2.8
52.5°	1.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222247

CATALOG NUMBER: LSR2B15NFL259730D010 2LBDLC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)