

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224639

Luminaire Tested: **LSR2B20FL408030D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B20FL408030D010 2LBDLC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1720.1 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224639

CATALOG NUMBER: LSR2B20FL408030D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224639

CATALOG NUMBER: LSR2B20FL408030D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83		
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	83	80	79		
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	76		
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72		
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69		
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67		
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1565730
5°	1535667
10°	1364117
15°	1076512
20°	717979
25°	413285
30°	209322
35°	98119
40°	40199
45°	18132
50°	9340
55°	5943
60°	3409
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224639

CATALOG NUMBER: LSR2B20FL408030D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.5	21.0
10°-20°	725.4	42.2
20°-30°	454.4	26.4
30°-40°	140.6	8.2
40°-50°	29.1	1.7
50°-60°	8.1	0.5
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1541.3	89.6
0°-40°	1681.9	97.8
0°-60°	1719.0	99.9
0°-90°	1720.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1720.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4042	
5°	3950	361
15°	2684	725
25°	967	454
35°	208	141
45°	33	29
55°	9	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224639

CATALOG NUMBER: LSR2B20FL408030D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4042.2
2.5°	4022.4
5°	3949.5
7.5°	3764.1
10°	3468.2
12.5°	3104.0
15°	2684.5
17.5°	2201.0
20°	1741.8
22.5°	1324.6
25°	967.0
27.5°	680.0
30°	468.0
32.5°	313.5
35°	207.5
37.5°	130.3
40°	79.5
42.5°	50.8
45°	33.1
47.5°	22.1
50°	15.5
52.5°	11.0
55°	8.8
57.5°	6.6
60°	4.4
62.5°	2.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)