

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224585

Luminaire Tested: **LSR2WM2B20FL408030D010 2LBDL*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224585
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408030D010 2LBDL*GPH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1763.7 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224585

CATALOG NUMBER: LSR2WM2B20FL408030D010 2LBDL*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P224585

CATALOG NUMBER: LSR2WM2B20FL408030D010 2LBDL*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100		108	104	101	98		101	99	96			98	96	94			91
3	106	100	96	93		104	99	95	92		96	93	91			94	92	89			87
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83		96	90	85	82		88	84	81			87	83	81			79
6	94	87	82	78		93	86	81	78		85	81	78			83	80	77			75
7	91	83	78	75		89	82	78	74		81	77	74			80	76	74			72
8	87	80	75	71		86	79	74	71		78	74	71			77	73	71			69
9	84	76	72	68		83	76	71	68		75	71	68			74	70	68			66
10	81	73	69	65		80	73	68	65		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1599971
5°	1567589
10°	1392948
15°	1092833
20°	735003
25°	427645
30°	214197
35°	99963
40°	46620
45°	19720
50°	9461
55°	6078
60°	3486
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224585

CATALOG NUMBER: LSR2WM2B20FL408030D010 2LBDL*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.0	20.9
10°-20°	739.7	41.9
20°-30°	467.7	26.5
30°-40°	145.5	8.3
40°-50°	32.3	1.8
50°-60°	8.2	0.5
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1576.5	89.4
0°-40°	1722.0	97.6
0°-60°	1762.6	99.9
0°-90°	1763.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1763.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4131	
5°	4032	369
15°	2725	740
25°	1001	468
35°	211	146
45°	36	32
55°	9	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224585

CATALOG NUMBER: LSR2WM2B20FL408030D010 2LBDL*GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4130.6
2.5°	4112.6
5°	4031.6
7.5°	3840.5
10°	3541.5
12.5°	3163.7
15°	2725.2
17.5°	2250.8
20°	1783.1
22.5°	1362.6
25°	1000.6
27.5°	701.5
30°	478.9
32.5°	317.0
35°	211.4
37.5°	141.7
40°	92.2
42.5°	56.2
45°	36.0
47.5°	24.7
50°	15.7
52.5°	11.2
55°	9.0
57.5°	6.7
60°	4.5
62.5°	2.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)