

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225007

Luminaire Tested: **LSR2WM2B20FL408030D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408030D010 2LBDL*LI
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1756.4 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225007

CATALOG NUMBER: LSR2WM2B20FL408030D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P225007

CATALOG NUMBER: LSR2WM2B20FL408030D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	105	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	96	93	104	99	95	92	97	94	91		94	92	90		92
4	102	96	91	88	100	95	90	87	93	89	86		91	88	85		89
5	98	91	86	83	97	90	86	83	89	85	82		87	84	81		86
6	94	87	82	79	93	86	82	79	85	81	78		84	80	78		83
7	91	83	79	75	90	83	78	75	82	78	75		81	77	74		80
8	88	80	75	72	87	80	75	72	79	74	71		78	74	71		77
9	85	77	72	69	84	76	72	69	76	71	69		75	71	68		74
10	82	74	69	66	81	74	69	66	73	69	66		72	68	66		72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1684839
5°	1619070
10°	1409428
15°	1100572
20°	731952
25°	419140
30°	208382
35°	95755
40°	38429
45°	17584
50°	8135
55°	4592
60°	2634
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225007

CATALOG NUMBER: LSR2WM2B20FL408030D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.0	21.6
10°-20°	744.2	42.4
20°-30°	460.6	26.2
30°-40°	137.8	7.8
40°-50°	27.6	1.6
50°-60°	6.7	0.4
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1583.8	90.2
0°-40°	1721.7	98.0
0°-60°	1756.0	100.0
0°-90°	1756.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1756.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4350	
5°	4164	379
15°	2744	744
25°	981	461
35°	202	138
45°	32	28
55°	7	7
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225007

CATALOG NUMBER: LSR2WM2B20FL408030D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4349.7
1°	4326.1
2°	4304.1
3°	4260.3
4°	4219.7
5°	4164.0
6°	4088.1
7°	3991.9
8°	3868.7
9°	3728.6
10°	3583.4
11°	3433.2
12°	3272.8
13°	3105.7
14°	2926.8
15°	2744.5
17.5°	2263.5
20°	1775.7
22.5°	1343.6
25°	980.7
27.5°	688.7
30°	465.9
32.5°	307.2
35°	202.5
37.5°	126.6
40°	76.0
42.5°	48.9
45°	32.1
47.5°	20.3
50°	13.5
52.5°	10.1
55°	6.8
57.5°	5.1
60°	3.4
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P225007

CATALOG NUMBER: LSR2WM2B20FL408030D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)