

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223396

Luminaire Tested: **LSR2WM2B20NFL258030D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20NFL258030D010 2LBDC*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1846.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223396

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223396

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	104	102	104	102	100		101	99	98		98
3	109	105	101	99	107	103	100	98	101	98	96		99	97	95		96
4	106	101	97	95	104	100	97	94	98	95	93		96	94	92		95
5	103	98	94	91	102	97	94	91	95	92	90		94	91	89		93
6	101	95	91	89	99	94	91	88	93	90	88		92	89	87		91
7	98	92	89	86	97	92	88	86	91	88	85		90	87	85		89
8	96	90	86	84	95	90	86	84	89	86	83		88	85	83		87
9	94	88	84	82	93	88	84	82	87	84	82		86	83	81		85
10	92	86	82	80	91	86	82	80	85	82	80		84	82	80		84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4242058
5°	3916796
10°	2651144
15°	901952
20°	331289
25°	175614
30°	90259
35°	42132
40°	13804
45°	6957
50°	3314
55°	1216
60°	1394
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223396

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	856.9	46.4
10°-20°	720.5	39.0
20°-30°	197.7	10.7
30°-40°	57.7	3.1
40°-50°	10.7	0.6
50°-60°	2.4	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1775.0	96.2
0°-40°	1832.7	99.3
0°-60°	1845.8	100.0
0°-90°	1846.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1846.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10952	
5°	10073	857
15°	2249	720
25°	411	198
35°	89	58
45°	13	11
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223396

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10951.6
1°	10888.0
2°	10775.2
3°	10613.4
4°	10391.6
5°	10073.4
6°	9638.8
7°	9095.1
8°	8431.5
9°	7647.8
10°	6740.4
11°	5745.8
12°	4711.2
13°	3723.9
14°	2882.0
15°	2249.2
17.5°	1269.2
20°	803.7
22.5°	572.8
25°	410.9
27.5°	290.9
30°	201.8
32.5°	141.8
35°	89.1
37.5°	36.4
40°	27.3
42.5°	20.0
45°	12.7
47.5°	7.3
50°	5.5
52.5°	3.6
55°	1.8
57.5°	1.8
60°	1.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223396

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)