

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225048

Luminaire Tested: **LSSQ2B15FL408040D010 2LBD\*WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225048  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14830)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B15FL408040D010 2LBD\*WMH  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1361.2 lumens  
Efficiency: N/A  
Efficacy: 95.2 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225048

CATALOG NUMBER: LSSQ2B15FL408040D010 2LBD\*WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P225048

CATALOG NUMBER: LSSQ2B15FL408040D010 2LBD\*WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91																
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87			87																
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82			82																
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79			79																
6	94	87	82	78	93	86	81	78	85	81	77	83	80	77	82	79	77	75			75																
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72			72																
8	87	79	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69			69																
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66			66																
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64			64																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1235208
5°	1209714
10°	1071683
15°	842121
20°	566205
25°	328919
30°	164371
35°	77502
40°	36659
45°	16050
50°	8316
55°	4660
60°	2711
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225048

CATALOG NUMBER: LSSQ2B15FL408040D010 2LBD\*WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	284.6	20.9
10°-20°	569.6	41.8
20°-30°	360.1	26.5
30°-40°	112.6	8.3
40°-50°	26.1	1.9
50°-60°	6.9	0.5
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1214.3	89.2
0°-40°	1326.9	97.5
0°-60°	1360.0	99.9
0°-90°	1361.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1361.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3189	
5°	3111	285
15°	2100	570
25°	770	360
35°	164	113
45°	29	26
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225048

CATALOG NUMBER: LSSQ2B15FL408040D010 2LBD\*WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3188.9
2.5°	3173.3
5°	3111.2
7.5°	2964.5
10°	2724.7
12.5°	2440.0
15°	2100.0
17.5°	1729.0
20°	1373.6
22.5°	1045.7
25°	769.6
27.5°	543.6
30°	367.5
32.5°	245.0
35°	163.9
37.5°	110.4
40°	72.5
42.5°	44.9
45°	29.3
47.5°	20.7
50°	13.8
52.5°	10.4
55°	6.9
57.5°	5.2
60°	3.5
62.5°	3.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)