

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223145

Luminaire Tested: **LSSQ2B15NFL258040D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B15NFL258040D010 2LBDC*MB
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1420.5 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223145

CATALOG NUMBER: LSSQ2B15NFL258040D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P223145

CATALOG NUMBER: LSSQ2B15NFL258040D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97				97															
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95				95															
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92				92															
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90				90															
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88				88															
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86				86															
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84				84															
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82				82															
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80				80															
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79				79															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3264281
5°	3013982
10°	2040080
15°	694068
20°	254908
25°	135140
30°	69461
35°	32438
40°	10619
45°	5368
50°	2531
55°	945
60°	1085
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223145

CATALOG NUMBER: LSSQ2B15NFL258040D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	659.4	46.4
10°-20°	554.4	39.0
20°-30°	152.1	10.7
30°-40°	44.4	3.1
40°-50°	8.2	0.6
50°-60°	1.9	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1365.9	96.2
0°-40°	1410.3	99.3
0°-60°	1420.3	100.0
0°-90°	1420.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1420.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8427	
5°	7752	659
15°	1731	554
25°	316	152
35°	69	44
45°	10	8
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223145

CATALOG NUMBER: LSSQ2B15NFL258040D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	8427.3
1°	8378.3
2°	8291.6
3°	8167.0
4°	7996.3
5°	7751.5
6°	7417.1
7°	6998.7
8°	6488.0
9°	5885.0
10°	5186.8
11°	4421.4
12°	3625.3
13°	2865.5
14°	2217.7
15°	1730.8
17.5°	976.6
20°	618.4
22.5°	440.7
25°	316.2
27.5°	223.9
30°	155.3
32.5°	109.1
35°	68.6
37.5°	28.0
40°	21.0
42.5°	15.4
45°	9.8
47.5°	5.6
50°	4.2
52.5°	2.8
55°	1.4
57.5°	1.4
60°	1.4
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223145

CATALOG NUMBER: LSSQ2B15NFL258040D010 2LBDC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)