

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2WM2B20WFL558030D010 2LBDLC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2WM2B20WFL558030D010 2LBDLC\*MW  
Description: 2000 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1586.8 lumens  
Efficiency: N/A  
Efficacy: 75.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558030D010 2LBDLC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558030D010 2LBDLC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 113 | 110 | 108 | 106 |  | 111 | 108 | 106 | 104 |  | 104 | 102 | 101 |  | 101 | 99  | 98  |  | 97  | 96  | 95  |
| 2   | 108 | 102 | 98  | 95  |  | 105 | 101 | 97  | 94  |  | 98  | 94  | 92  |  | 95  | 92  | 90  |  | 92  | 90  | 88  |
| 3   | 102 | 95  | 90  | 86  |  | 100 | 94  | 89  | 85  |  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 87  | 84  | 81  |
| 4   | 97  | 89  | 83  | 79  |  | 95  | 88  | 82  | 78  |  | 85  | 81  | 77  |  | 83  | 80  | 76  |  | 82  | 78  | 76  |
| 5   | 91  | 83  | 77  | 72  |  | 90  | 82  | 76  | 72  |  | 80  | 75  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |
| 6   | 87  | 78  | 71  | 67  |  | 85  | 77  | 71  | 67  |  | 75  | 70  | 66  |  | 74  | 69  | 66  |  | 73  | 69  | 65  |
| 7   | 82  | 73  | 67  | 62  |  | 81  | 72  | 66  | 62  |  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 64  | 61  |
| 8   | 78  | 69  | 62  | 58  |  | 77  | 68  | 62  | 58  |  | 67  | 62  | 58  |  | 66  | 61  | 58  |  | 65  | 61  | 57  |
| 9   | 74  | 65  | 59  | 55  |  | 73  | 64  | 58  | 54  |  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 61  | 57  | 54  |
| 10  | 71  | 61  | 55  | 51  |  | 70  | 61  | 55  | 51  |  | 60  | 55  | 51  |  | 59  | 54  | 51  |  | 58  | 54  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 744363 |
| 5°  | 739585 |
| 10° | 687605 |
| 15° | 603600 |
| 20° | 520326 |
| 25° | 444955 |
| 30° | 353119 |
| 35° | 246125 |
| 40° | 155738 |
| 45° | 95042  |
| 50° | 56223  |
| 55° | 30727  |
| 60° | 6740   |
| 65° | 5958   |
| 70° | 4870   |
| 75° | 6435   |
| 80° | 4907   |
| 85° | 9777   |



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558030D010 2LBDLC\*MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 176.5  | 11.1      |
| 10°-20°   | 419.2  | 26.4      |
| 20°-30°   | 473.0  | 29.8      |
| 30°-40°   | 327.2  | 20.6      |
| 40°-50°   | 139.5  | 8.8       |
| 50°-60°   | 40.3   | 2.5       |
| 60°-70°   | 5.9    | 0.4       |
| 70°-80°   | 3.7    | 0.2       |
| 80°-90°   | 1.5    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1068.7 | 67.4      |
| 0°-40°    | 1395.9 | 88.0      |
| 0°-60°    | 1575.7 | 99.3      |
| 0°-90°    | 1586.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1586.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1922 |      |
| 5°  | 1902 | 177  |
| 15° | 1505 | 419  |
| 25° | 1041 | 473  |
| 35° | 520  | 327  |
| 45° | 174  | 139  |
| 55° | 46   | 40   |
| 65° | 6    | 6    |
| 75° | 4    | 4    |
| 85° | 2    | 1    |
| 90° | 0    |      |



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558030D010 2LBDLC\*MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1921.7 |
| 2.5°  | 1919.5 |
| 5°    | 1902.1 |
| 7.5°  | 1843.6 |
| 10°   | 1748.2 |
| 12.5° | 1631.0 |
| 15°   | 1505.2 |
| 17.5° | 1375.1 |
| 20°   | 1262.3 |
| 22.5° | 1156.0 |
| 25°   | 1041.1 |
| 27.5° | 919.6  |
| 30°   | 789.5  |
| 32.5° | 648.5  |
| 35°   | 520.5  |
| 37.5° | 403.4  |
| 40°   | 308.0  |
| 42.5° | 232.1  |
| 45°   | 173.5  |
| 47.5° | 125.8  |
| 50°   | 93.3   |
| 52.5° | 67.2   |
| 55°   | 45.5   |
| 57.5° | 19.5   |
| 60°   | 8.7    |
| 62.5° | 6.5    |
| 65°   | 6.5    |
| 67.5° | 4.3    |
| 70°   | 4.3    |
| 72.5° | 4.3    |
| 75°   | 4.3    |
| 77.5° | 2.2    |
| 80°   | 2.2    |
| 82.5° | 2.2    |
| 85°   | 2.2    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)