

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224730

Luminaire Tested: **LSSQWM2B15FL408040D010 2LBD\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224730  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B15FL408040D010 2LBD\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1445.8 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224730

CATALOG NUMBER: LSSQWM2B15FL408040D010 2LBD\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224730

CATALOG NUMBER: LSSQWM2B15FL408040D010 2LBD\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91				91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86				86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82				82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79				79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75				75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72				72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69				69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66				66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64				64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1308803
5°	1284952
10°	1142284
15°	898343
20°	597780
25°	343193
30°	173361
35°	81569
40°	32816
45°	16269
50°	8919
55°	6280
60°	5733
65°	3391
70°	4190
75°	2844
80°	4238
85°	0



TEST NUMBER: P224730

CATALOG NUMBER: LSSQWM2B15FL408040D010 2LBD\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	302.7	20.9
10°-20°	606.8	42.0
20°-30°	377.5	26.1
30°-40°	116.1	8.0
40°-50°	25.5	1.8
50°-60°	9.1	0.6
60°-70°	4.6	0.3
70°-80°	2.7	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1287.0	89.0
0°-40°	1403.1	97.1
0°-60°	1437.7	99.4
0°-90°	1445.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1445.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3379	
5°	3305	303
15°	2240	607
25°	803	378
35°	172	116
45°	30	26
55°	9	9
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224730

CATALOG NUMBER: LSSQWM2B15FL408040D010 2LBD\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3378.9
2.5°	3364.1
5°	3304.7
7.5°	3154.5
10°	2904.2
12.5°	2603.7
15°	2240.2
17.5°	1843.4
20°	1450.2
22.5°	1099.7
25°	803.0
27.5°	565.6
30°	387.6
32.5°	261.5
35°	172.5
37.5°	103.9
40°	64.9
42.5°	44.5
45°	29.7
47.5°	20.4
50°	14.8
52.5°	13.0
55°	9.3
57.5°	7.4
60°	7.4
62.5°	5.6
65°	3.7
67.5°	3.7
70°	3.7
72.5°	3.7
75°	1.9
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)