

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224488

Luminaire Tested: **LSSQ2B20FL408030D010 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B20FL408030D010 2LBDL*WH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1786.8 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224488

CATALOG NUMBER: LSSQ2B20FL408030D010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224488

CATALOG NUMBER: LSSQ2B20FL408030D010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82		
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79		
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75		
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72		
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66		
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1648661
5°	1586292
10°	1396252
15°	1096722
20°	745638
25°	435424
30°	221756
35°	104928
40°	45811
45°	19830
50°	9521
55°	6145
60°	3486
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224488

CATALOG NUMBER: LSSQ2B20FL408030D010 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	372.6	20.9
10°-20°	743.7	41.6
20°-30°	477.4	26.7
30°-40°	151.5	8.5
40°-50°	32.3	1.8
50°-60°	8.3	0.5
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1593.6	89.2
0°-40°	1745.1	97.7
0°-60°	1785.7	99.9
0°-90°	1786.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1786.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4256	
5°	4080	373
15°	2735	744
25°	1019	477
35°	222	151
45°	36	32
55°	9	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224488

CATALOG NUMBER: LSSQ2B20FL408030D010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4256.3
2.5°	4215.5
5°	4079.7
7.5°	3857.8
10°	3549.9
12.5°	3174.1
15°	2734.9
17.5°	2266.2
20°	1808.9
22.5°	1381.0
25°	1018.8
27.5°	726.7
30°	495.8
32.5°	332.8
35°	221.9
37.5°	147.2
40°	90.6
42.5°	56.6
45°	36.2
47.5°	24.9
50°	15.8
52.5°	11.3
55°	9.1
57.5°	6.8
60°	4.5
62.5°	2.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)