

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B15WFL558040D010 2LBDC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B15WFL558040D010 2LBDC\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1368.4 lumens  
Efficiency: N/A  
Efficacy: 95.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558040D010 2LBDC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558040D010 2LBDC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 93  |
| 2   | 108 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 94  | 92  | 95  | 92  | 90  | 92  | 90  | 88  | 86  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  | 89  | 85  | 83  | 87  | 84  | 81  | 80  |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 82  | 78  | 85  | 81  | 77  | 83  | 80  | 76  | 82  | 78  | 76  | 74  |
| 5   | 91  | 83  | 77  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 69  |
| 6   | 87  | 78  | 71  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  | 74  | 69  | 66  | 73  | 69  | 65  | 64  |
| 7   | 82  | 73  | 67  | 62  | 81  | 72  | 66  | 62  | 71  | 66  | 62  | 70  | 65  | 62  | 69  | 64  | 61  | 60  |
| 8   | 78  | 69  | 62  | 58  | 77  | 68  | 62  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 57  | 56  |
| 9   | 74  | 65  | 59  | 55  | 73  | 64  | 58  | 54  | 63  | 58  | 54  | 62  | 57  | 54  | 61  | 57  | 54  | 53  |
| 10  | 71  | 61  | 55  | 51  | 70  | 61  | 55  | 51  | 60  | 55  | 51  | 59  | 54  | 51  | 58  | 54  | 51  | 49  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 641910 |
| 5°  | 637791 |
| 10° | 592932 |
| 15° | 520551 |
| 20° | 448726 |
| 25° | 383710 |
| 30° | 304500 |
| 35° | 212268 |
| 40° | 134299 |
| 45° | 81949  |
| 50° | 48449  |
| 55° | 26540  |
| 60° | 5810   |
| 65° | 5133   |
| 70° | 4190   |
| 75° | 5537   |
| 80° | 4238   |
| 85° | 8444   |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558040D010 2LBDC\*MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 152.2  | 11.1      |
| 10°-20°   | 361.5  | 26.4      |
| 20°-30°   | 407.9  | 29.8      |
| 30°-40°   | 282.2  | 20.6      |
| 40°-50°   | 120.3  | 8.8       |
| 50°-60°   | 34.8   | 2.5       |
| 60°-70°   | 5.1    | 0.4       |
| 70°-80°   | 3.2    | 0.2       |
| 80°-90°   | 1.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 921.6  | 67.4      |
| 0°-40°    | 1203.8 | 88.0      |
| 0°-60°    | 1358.8 | 99.3      |
| 0°-90°    | 1368.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1368.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1657 |      |
| 5°  | 1640 | 152  |
| 15° | 1298 | 362  |
| 25° | 898  | 408  |
| 35° | 449  | 282  |
| 45° | 150  | 120  |
| 55° | 39   | 35   |
| 65° | 6    | 5    |
| 75° | 4    | 3    |
| 85° | 2    | 1    |
| 90° | 0    |      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558040D010 2LBDC\*MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1657.2 |
| 2.5°  | 1655.3 |
| 5°    | 1640.3 |
| 7.5°  | 1589.8 |
| 10°   | 1507.5 |
| 12.5° | 1406.5 |
| 15°   | 1298.1 |
| 17.5° | 1185.8 |
| 20°   | 1088.6 |
| 22.5° | 996.9  |
| 25°   | 897.8  |
| 27.5° | 793.1  |
| 30°   | 680.8  |
| 32.5° | 559.3  |
| 35°   | 448.9  |
| 37.5° | 347.9  |
| 40°   | 265.6  |
| 42.5° | 200.1  |
| 45°   | 149.6  |
| 47.5° | 108.5  |
| 50°   | 80.4   |
| 52.5° | 58.0   |
| 55°   | 39.3   |
| 57.5° | 16.8   |
| 60°   | 7.5    |
| 62.5° | 5.6    |
| 65°   | 5.6    |
| 67.5° | 3.7    |
| 70°   | 3.7    |
| 72.5° | 3.7    |
| 75°   | 3.7    |
| 77.5° | 1.9    |
| 80°   | 1.9    |
| 82.5° | 1.9    |
| 85°   | 1.9    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)