

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225054

Luminaire Tested: **LSSQWM2B20FL408030D010 2LBD\*WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225054  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14830)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B20FL408030D010 2LBD\*WMH  
Description: 2000 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1744.3 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225054

CATALOG NUMBER: LSSQWM2B20FL408030D010 2LBD\*WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P225054

CATALOG NUMBER: LSSQWM2B20FL408030D010 2LBD\*WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  | 98  | 97  |
| 2   | 110 | 106 | 102 | 100 |  | 108 | 104 | 101 | 98  |  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  | 94  | 92  |
| 3   | 106 | 100 | 96  | 93  |  | 104 | 99  | 95  | 92  |  | 96  | 93  | 91  |  | 94  | 91  | 89  |  | 92  | 90  | 88  |
| 4   | 102 | 95  | 91  | 87  |  | 100 | 94  | 90  | 87  |  | 92  | 89  | 86  |  | 90  | 87  | 85  |  | 88  | 86  | 84  |
| 5   | 98  | 91  | 86  | 82  |  | 96  | 90  | 85  | 82  |  | 88  | 84  | 81  |  | 87  | 83  | 81  |  | 85  | 82  | 80  |
| 6   | 94  | 87  | 82  | 78  |  | 93  | 86  | 81  | 78  |  | 85  | 81  | 77  |  | 83  | 80  | 77  |  | 82  | 79  | 77  |
| 7   | 91  | 83  | 78  | 75  |  | 89  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 80  | 76  | 74  |  | 79  | 76  | 73  |
| 8   | 87  | 79  | 75  | 71  |  | 86  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 71  |  | 76  | 73  | 70  |
| 9   | 84  | 76  | 71  | 68  |  | 83  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 68  |  | 73  | 70  | 67  |
| 10  | 81  | 73  | 69  | 65  |  | 80  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 67  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1582812 |
| 5°  | 1550170 |
| 10° | 1373282 |
| 15° | 1079158 |
| 20° | 725522  |
| 25° | 421491  |
| 30° | 210664  |
| 35° | 99348   |
| 40° | 46974   |
| 45° | 20597   |
| 50° | 10666   |
| 55° | 5943    |
| 60° | 3409    |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P225054

CATALOG NUMBER: LSSQWM2B20FL408030D010 2LBD\*WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 364.8  | 20.9      |
| 10°-20°   | 729.9  | 41.8      |
| 20°-30°   | 461.4  | 26.5      |
| 30°-40°   | 144.3  | 8.3       |
| 40°-50°   | 33.5   | 1.9       |
| 50°-60°   | 8.8    | 0.5       |
| 60°-70°   | 1.6    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1556.0 | 89.2      |
| 0°-40°    | 1700.4 | 97.5      |
| 0°-60°    | 1742.7 | 99.9      |
| 0°-90°    | 1744.3 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1744.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4086 |      |
| 5°  | 3987 | 365  |
| 15° | 2691 | 730  |
| 25° | 986  | 461  |
| 35° | 210  | 144  |
| 45° | 38   | 34   |
| 55° | 9    | 9    |
| 65° | 0    | 2    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P225054

CATALOG NUMBER: LSSQWM2B20FL408030D010 2LBD\*WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 4086.3 |
| 2.5°  | 4066.4 |
| 5°    | 3986.8 |
| 7.5°  | 3798.9 |
| 10°   | 3491.5 |
| 12.5° | 3126.7 |
| 15°   | 2691.1 |
| 17.5° | 2215.6 |
| 20°   | 1760.1 |
| 22.5° | 1340.0 |
| 25°   | 986.2  |
| 27.5° | 696.5  |
| 30°   | 471.0  |
| 32.5° | 314.0  |
| 35°   | 210.1  |
| 37.5° | 141.5  |
| 40°   | 92.9   |
| 42.5° | 57.5   |
| 45°   | 37.6   |
| 47.5° | 26.5   |
| 50°   | 17.7   |
| 52.5° | 13.3   |
| 55°   | 8.8    |
| 57.5° | 6.6    |
| 60°   | 4.4    |
| 62.5° | 4.4    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)