

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225076

Luminaire Tested: **LSR2B15FL409040D010 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14829)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15FL409040D010 2LBD*WH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1197.8 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225076

CATALOG NUMBER: LSR2B15FL409040D010 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P225076

CATALOG NUMBER: LSR2B15FL409040D010 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91																
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87			87																
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82			82																
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79			79																
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75			75																
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72			72																
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69																
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66			66																
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1105176
5°	1063360
10°	935987
15°	735172
20°	499840
25°	291864
30°	148672
35°	70315
40°	30693
45°	13311
50°	6388
55°	4119
60°	2324
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225076

CATALOG NUMBER: LSR2B15FL409040D010 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.8	20.9
10°-20°	498.5	41.6
20°-30°	320.0	26.7
30°-40°	101.5	8.5
40°-50°	21.7	1.8
50°-60°	5.6	0.5
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1068.3	89.2
0°-40°	1169.8	97.7
0°-60°	1197.1	99.9
0°-90°	1197.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1197.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2853	
5°	2735	250
15°	1833	499
25°	683	320
35°	149	102
45°	24	22
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225076

CATALOG NUMBER: LSR2B15FL409040D010 2LBD*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2853.2
2.5°	2825.9
5°	2734.8
7.5°	2586.1
10°	2379.7
12.5°	2127.7
15°	1833.3
17.5°	1519.2
20°	1212.6
22.5°	925.8
25°	682.9
27.5°	487.2
30°	332.4
32.5°	223.1
35°	148.7
37.5°	98.6
40°	60.7
42.5°	37.9
45°	24.3
47.5°	16.7
50°	10.6
52.5°	7.6
55°	6.1
57.5°	4.6
60°	3.0
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)