

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222583

Luminaire Tested: **LSR2B15NFL259040D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15NFL259040D010 2LBDLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1095.5 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222583

CATALOG NUMBER: LSR2B15NFL259040D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P222583

CATALOG NUMBER: LSR2B15NFL259040D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97									97																		
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95									95																		
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92									92																		
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90									90																		
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88									88																		
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86									86																		
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84									84																		
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82									82																		
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80									80																		
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79									79																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2517439
5°	2324399
10°	1573325
15°	535268
20°	196581
25°	104240
30°	53583
35°	25014
40°	8191
45°	4163
50°	1928
55°	743
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222583

CATALOG NUMBER: LSR2B15NFL259040D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	508.5	46.4
10°-20°	427.5	39.0
20°-30°	117.3	10.7
30°-40°	34.2	3.1
40°-50°	6.3	0.6
50°-60°	1.5	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1053.4	96.2
0°-40°	1087.6	99.3
0°-60°	1095.4	100.0
0°-90°	1095.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1095.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6499	
5°	5978	509
15°	1335	428
25°	244	117
35°	53	34
45°	8	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222583

CATALOG NUMBER: LSR2B15NFL259040D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	6499.2
1°	6461.4
2°	6394.5
3°	6298.5
4°	6166.8
5°	5978.0
6°	5720.1
7°	5397.5
8°	5003.6
9°	4538.5
10°	4000.1
11°	3409.8
12°	2795.8
13°	2209.9
14°	1710.3
15°	1334.8
17.5°	753.2
20°	476.9
22.5°	339.9
25°	243.9
27.5°	172.6
30°	119.8
32.5°	84.2
35°	52.9
37.5°	21.6
40°	16.2
42.5°	11.9
45°	7.6
47.5°	4.3
50°	3.2
52.5°	2.2
55°	1.1
57.5°	1.1
60°	1.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222583

CATALOG NUMBER: LSR2B15NFL259040D010 2LBDLC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)