

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B15WFL559040D010 2LBD\*WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14805)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B15WFL559040D010 2LBD\*WMH  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1106.2 lumens  
Efficiency: N/A  
Efficacy: 77.4 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#  
CATALOG NUMBER: LSR2B15WFL559040D010 2LBD\*WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559040D010 2LBD\*WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80		
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74		
5	92	83	77	73	90	82	77	72	80	75	72	79	74	71	77	73	70	69		
6	87	78	72	67	85	77	71	67	75	70	67	74	70	66	73	69	66	64		
7	82	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60		
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56		
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53		
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	526829
5°	520560
10°	481150
15°	421702
20°	363936
25°	309814
30°	245372
35°	170325
40°	110635
45°	66611
50°	38446
55°	21543
60°	9451
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559040D010 2LBD\*WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.1	11.2
10°-20°	293.0	26.5
20°-30°	329.8	29.8
30°-40°	227.8	20.6
40°-50°	98.7	8.9
50°-60°	30.6	2.8
60°-70°	2.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	746.9	67.5
0°-40°	974.7	88.1
0°-60°	1104.0	99.8
0°-90°	1106.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1106.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1360	
5°	1339	124
15°	1052	293
25°	725	330
35°	360	228
45°	122	99
55°	32	31
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559040D010 2LBD\*WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1360.1
2.5°	1357.0
5°	1338.8
7.5°	1296.2
10°	1223.3
12.5°	1139.7
15°	1051.6
17.5°	960.4
20°	882.9
22.5°	805.4
25°	724.9
27.5°	642.8
30°	548.6
32.5°	449.8
35°	360.2
37.5°	282.7
40°	218.8
42.5°	165.6
45°	121.6
47.5°	89.7
50°	63.8
52.5°	45.6
55°	31.9
57.5°	22.8
60°	12.2
62.5°	3.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)