

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224745

Luminaire Tested: **LSR2WM2B20FL409030D010 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL409030D010 2LBD*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1494.8 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224745

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224745

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92
4	101	95	90	87	100	94	90	86	92	88	85		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		86	83	80		85
6	94	87	82	78	93	86	81	78	84	80	77		83	80	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1353271
5°	1328617
10°	1181066
15°	928860
20°	618101
25°	354861
30°	179265
35°	84311
40°	33929
45°	16817
50°	9220
55°	6483
60°	5965
65°	3483
70°	4304
75°	2844
80°	4238
85°	0



TEST NUMBER: P224745

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.9	20.9
10°-20°	627.4	42.0
20°-30°	390.4	26.1
30°-40°	120.0	8.0
40°-50°	26.4	1.8
50°-60°	9.4	0.6
60°-70°	4.7	0.3
70°-80°	2.8	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1330.7	89.0
0°-40°	1450.8	97.1
0°-60°	1486.5	99.4
0°-90°	1494.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1494.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3494	
5°	3417	313
15°	2316	627
25°	830	390
35°	178	120
45°	31	26
55°	10	9
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224745

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3493.7
2.5°	3478.3
5°	3417.0
7.5°	3261.7
10°	3002.8
12.5°	2692.2
15°	2316.3
17.5°	1906.0
20°	1499.5
22.5°	1137.1
25°	830.3
27.5°	584.8
30°	400.8
32.5°	270.4
35°	178.3
37.5°	107.4
40°	67.1
42.5°	46.0
45°	30.7
47.5°	21.1
50°	15.3
52.5°	13.4
55°	9.6
57.5°	7.7
60°	7.7
62.5°	5.8
65°	3.8
67.5°	3.8
70°	3.8
72.5°	3.8
75°	1.9
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)