

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224736

Luminaire Tested: **LSRWM2B15FL409040D010 2LBD\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224736  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSRWM2B15FL409040D010 2LBD\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1174.5 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224736

CATALOG NUMBER: LSRWM2B15FL409040D010 2LBD\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224736

CATALOG NUMBER: LSRWM2B15FL409040D010 2LBD\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1063303
5°	1043919
10°	928003
15°	729838
20°	485660
25°	278829
30°	140845
35°	66248
40°	26647
45°	13202
50°	7292
55°	5065
60°	4648
65°	2750
70°	3398
75°	2245
80°	3346
85°	0



TEST NUMBER: P224736

CATALOG NUMBER: LSRWM2B15FL409040D010 2LBD\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	245.9	20.9
10°-20°	493.0	42.0
20°-30°	306.7	26.1
30°-40°	94.3	8.0
40°-50°	20.7	1.8
50°-60°	7.4	0.6
60°-70°	3.7	0.3
70°-80°	2.2	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1045.6	89.0
0°-40°	1139.9	97.1
0°-60°	1168.0	99.4
0°-90°	1174.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1174.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2745	
5°	2685	246
15°	1820	493
25°	652	307
35°	140	94
45°	24	21
55°	8	7
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P224736

CATALOG NUMBER: LSRWM2B15FL409040D010 2LBD\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2745.1
2.5°	2733.0
5°	2684.8
7.5°	2562.8
10°	2359.4
12.5°	2115.3
15°	1820.0
17.5°	1497.6
20°	1178.2
22.5°	893.4
25°	652.4
27.5°	459.5
30°	314.9
32.5°	212.4
35°	140.1
37.5°	84.4
40°	52.7
42.5°	36.2
45°	24.1
47.5°	16.6
50°	12.1
52.5°	10.5
55°	7.5
57.5°	6.0
60°	6.0
62.5°	4.5
65°	3.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	1.5
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)