

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225158

Luminaire Tested: **LSSQWM2B20FL409030D010 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL409030D010 2LBD*GPH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1514.1 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225158

CATALOG NUMBER: LSSQWM2B20FL409030D010 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P225158

CATALOG NUMBER: LSSQWM2B20FL409030D010 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	100		108	104	101	98		101	99	96			98	96	94			95
3	106	100	96	93		104	99	95	92		96	93	91			94	92	89			92
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			89
5	98	91	86	83		96	90	85	82		88	84	81			87	83	81			85
6	94	87	82	78		93	86	81	78		85	81	78			83	80	77			82
7	91	83	78	75		89	82	78	74		81	77	74			80	76	74			79
8	87	80	75	71		86	79	74	71		78	74	71			77	73	71			76
9	84	76	72	68		83	76	71	68		75	71	68			74	70	68			73
10	81	73	69	65		80	73	68	65		72	68	65			72	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1373529
5°	1345764
10°	1195815
15°	938203
20°	631003
25°	367127
30°	183917
35°	85824
40°	39996
45°	16927
50°	8135
55°	5200
60°	3021
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225158

CATALOG NUMBER: LSSQWM2B20FL409030D010 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	316.8	20.9
10°-20°	635.1	41.9
20°-30°	401.6	26.5
30°-40°	124.9	8.3
40°-50°	27.8	1.8
50°-60°	7.1	0.5
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1353.4	89.4
0°-40°	1478.4	97.6
0°-60°	1513.2	99.9
0°-90°	1514.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1514.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3546	
5°	3461	317
15°	2340	635
25°	859	402
35°	182	125
45°	31	28
55°	8	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225158

CATALOG NUMBER: LSSQWM2B20FL409030D010 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3546.0
2.5°	3530.6
5°	3461.1
7.5°	3297.0
10°	3040.3
12.5°	2716.0
15°	2339.6
17.5°	1932.3
20°	1530.8
22.5°	1169.8
25°	859.0
27.5°	602.3
30°	411.2
32.5°	272.2
35°	181.5
37.5°	121.6
40°	79.1
42.5°	48.3
45°	30.9
47.5°	21.2
50°	13.5
52.5°	9.7
55°	7.7
57.5°	5.8
60°	3.9
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)