

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224878

Luminaire Tested: **LSSQ2B15FL409040D010 2LBD\*B**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224878  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B15FL409040D010 2LBD\*B  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1160.1 lumens  
Efficiency: N/A  
Efficacy: 81.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224878

CATALOG NUMBER: LSSQ2B15FL409040D010 2LBD\*B

### Luminous Intensity Polar Plot





TEST NUMBER: P224878

CATALOG NUMBER: LSSQ2B15FL409040D010 2LBD\*B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	96	94	92	91			91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87			87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83			83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79			79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72			72
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69			69
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67			67
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1049669
5°	1031399
10°	920097
15°	727272
20°	484918
25°	281350
30°	140800
35°	66248
40°	25889
45°	11558
50°	5423
55°	3039
60°	1162
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224878

CATALOG NUMBER: LSSQ2B15FL409040D010 2LBD\*B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	243.1	21.0
10°-20°	490.9	42.3
20°-30°	308.8	26.6
30°-40°	94.4	8.1
40°-50°	18.5	1.6
50°-60°	4.1	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1042.8	89.9
0°-40°	1137.2	98.0
0°-60°	1159.9	100.0
0°-90°	1160.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1160.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2710	
5°	2653	243
15°	1814	491
25°	658	309
35°	140	94
45°	21	19
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224878

CATALOG NUMBER: LSSQ2B15FL409040D010 2LBD\*B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2709.9
2.5°	2703.8
5°	2652.6
7.5°	2532.1
10°	2339.3
12.5°	2098.3
15°	1813.6
17.5°	1497.3
20°	1176.4
22.5°	902.3
25°	658.3
27.5°	463.9
30°	314.8
32.5°	212.4
35°	140.1
37.5°	85.9
40°	51.2
42.5°	33.1
45°	21.1
47.5°	13.6
50°	9.0
52.5°	6.0
55°	4.5
57.5°	3.0
60°	1.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)